






REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		产品外观变更，图面升级整理图面	2025.04.09	阿树



U255-05XN-4BH73-XS

1:AU 1U''
5:AU 15U''
6:AU 30U''

S:SUS
F:Flat



- 备注:
- 1.产品规格:
- 1-1.Insertion force(插入力): 35NMAX.
 - 1-2.extraction force(拔出力) :10NMIN.INITIAL8-20NAFTER
 - 1-3.Current rating(额定电流) : 1.0A
 - 1-4.Rated voltage(额定电压) : 30V
 - 1-5.durability(耐久性) : 10000CYCLESMIN.
 - 1-6.Withstand voltage(耐电压) : 100VACMIN
 - 1-7.Contact resistance(接触阻抗) : 30mQMAX.INITIAL: 40mQMAX AFTER
 - 1-8.Insulation resistance(绝缘电阻) : 100MQMIN
 - 1-9.Temperature range(工作温度) : -30°TO+80°
- 2.Material(材质) :
- 2.1Gel core(胶芯) : LCPUL94V-0
 - 2.2Terminal(端子) : C2680R-H, Nickel base, gold plating1μ
 - 2.3Housing(外壳) : SUS201/301, Matte tin/nickel plating on the surface

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树	VIEW:	MODEL TYPE: MICRO USB
CHECKED		UNIT: mm/in	PART NO.: U255-05XN-4BH73-FS
APPROVED		SIZE: A4	DWG NO.: