








标 记
MARKECN编号/变更内容
ECN NO/DEFINITION修 改
REVISE日 期
DATE核 准
APPROVE

No. of Contacts	DIM A	DIM B	DIM C
2	1.25	3.85	5.75
3	2.50	5.10	7.00
4	3.75	6.35	8.25
5	5.00	7.60	9.50
6	6.25	8.85	10.75
7	7.50	10.10	12.00
8	8.75	11.35	13.25
9	10.00	12.60	14.50
10	11.25	13.85	15.75
11	12.50	15.10	17.00
12	13.75	16.35	18.25
13	15.00	17.60	19.50
14	16.25	18.85	20.75
15	17.50	20.10	22.00
16	18.75	21.35	23.25



技术要求:

额定电流: 1.0A AC,DC
(注: AWG32# 0.8)

额定电压: 50V AC

温度范围: -25°C~85°C

接触电阻: ≤0.02Ω






绝缘电阻: ≥100MΩ

耐 压: 500V AC/min

材 料:

塑胶 LCP, 米色

金属 铜合金, 镀锡



2	插针	铜	镀锡	
1	基座	LCP	米色	
序号	品名	材质	电镀/颜色	备注



深圳市虹成电子有限公司

品 名
TITLE
料 号
PART NO

针座

HCZZ0014-10

GENERAL TOLERANCES
(UNLESS SPECIFIED)比 例
SCALE

1:1

X.±0.30 X.±5°
.X±0.25 .X±3°
.XX±0.20 .XX±1°单 位
UNIT
张 数
PART NO
版 本
REVMM
1 OF 1
A制 图
DRAW
审 核
CHECKED
批 准
APPROVEAhYe
夏操云
赵亮亮