



RoHS

REV	ECN NO.	DESCRIPTION	DESIGN	APPROVAL	DATE
A1	NEW	更换图框			2024.05.24

- SPECIFICATIONS
- Current rating: 7A
 - Temperature range: -40°C ~ +105°C
 - Insulation resistance: 1000MΩ Min.
 - Withstanding voltage: 1000V AC/ minute.
 - Contact resistance: 20mΩ Max.

Material:
Insulator Material:PA9T(UL 94V-0)
Contact Material:Brass
Plating:Matte Tin or gold plated over Nickel
Mate with XFCN PZ396 Single row series

Ordering Code:
PM396V-11-XX-H889
1.序列号
2.Pin位数: 02-20P



X.±0.50	X.°±	PART NO: PM396V-11-XX-H889		XFCN 兴飞连接器											
.X±0.25	.X°±														
.XX±0.15	.XX°±														
.XXX±0.10	.XXX°±														
UNITS:	mm	TITLE: 3.96mm Female Header Connectors		0769-82001899											
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF XFCN AND SHALL NOT BE REPRODUCED, COPIED OR CUED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF XFCN				www.xfconn.com											
				DWG NO: /											
APPD		Chen ZhiQiang		VIEW											
								CHKD		Liu Wei					
												DRAW		Chen HongJiang	
SCALE		NONE													
				SHEET		1/1									
								REV		A1					