




| REV. | EC# | DESCRIPTION | DATE DRAWN | CHECK | APPROVED |
|------|-----|-------------|------------|-------|----------|
| 1.00 |     | 初版发行        | 2020-8-28  |       |          |
|      |     |             |            |       |          |
|      |     |             |            |       |          |

|                |       |       |       |
|----------------|-------|-------|-------|
| 15P            | 40    | 38.6  | 35    |
| 14P            | 37.5  | 36.1  | 32.5  |
| 13P            | 35    | 33.6  | 30    |
| 12P            | 32.5  | 31.1  | 27.5  |
| 11P            | 30    | 28.6  | 25    |
| 10P            | 27.5  | 26.1  | 22.5  |
| 9P             | 25    | 23.6  | 20    |
| 8P             | 22.5  | 21.1  | 17.5  |
| 7P             | 20    | 18.6  | 15    |
| 6P             | 17.5  | 16.1  | 12.5  |
| 5P             | 15    | 13.6  | 10    |
| 4P             | 12.5  | 11.1  | 7.5   |
| 3P             | 10    | 8.6   | 5     |
| 2P             | 7.5   | 6.1   | 2.5   |
| NUMBER OF PINS | DIM.A | DIM.B | DIM.C |

技术要求:

- 1) 材质: 见附表;
- 2) 电镀: 见附表;
- 3) 塑件表面平整、光洁、无毛刺、气泡、烧焦、变形、浇口无拉伤、多料或缺料等不良现象;
- 4) 端子表面无氧化、电镀不良等现象。

适应基板厚度: 1.2mm~1.6mm

温度范围: -25℃~85℃

额定电压: 250V AC/DC

额定电流: 3A

接触电阻: ≤0.01Ω

绝缘电阻: ≥1000MΩ

耐 压: 1000V AC/minute

|                                                                                                                                                  |         |            |                            |
|--------------------------------------------------------------------------------------------------------------------------------------------------|---------|------------|----------------------------|
| 2                                                                                                                                                | PIN     | n PCS      | 材质: 黄铜, 电镀: 镀亮锡60u"MIN     |
| 1                                                                                                                                                | Housing | 1 PCS      | 材质: PA66 (UL94V-0), 颜色: 本色 |
| NO.                                                                                                                                              | NAME    | Q'TY       | DESCRIPTION                |
| <div><div> 韩下®<br/>HANXIA</div><div>深圳市韩下电子有限公司</div></div> |         |            |                            |
| DRAW :                                                                                                                                           | 黄彬      | 2020-8-28  | TITLE: HX-XHB2.54-8PZZ     |
| DESIGN:                                                                                                                                          |         |            |                            |
| CHECK:                                                                                                                                           | 张伟      | 2020-8-28  | SERIES: 1501 SERIES        |
| APPROVED                                                                                                                                         | 罗小春     | 2020-8-28  | P/N:                       |
| CUSTOMER DRAWING                                                                                                                                 |         | REV. 1.00  | SCALE N/A                  |
|                                                                                                                                                  |         | DRAW NAME: | 插件针座                       |
|                                                                                                                                                  |         | DRAW NO.   |                            |
|                                                                                                                                                  |         | UNIT: mm   | SHEET: 1/1                 |