




	INCHES		MILLIMETERS	
15P	40	38.6	35	
14P	37.5	36.1	32.5	
13P	35	33.6	30	
12P	32.5	31.1	27.5	
11P	30	28.6	25	
10P	27.5	26.1	22.5	
9P	25	23.6	20	
8P	22.5	21.1	17.5	
7P	20	18.6	15	
6P	17.5	16.1	12.5	
5P	15	13.6	10	
4P	12.5	11.1	7.5	
3P	10	8.6	5	
2P	7.5	6.1	2.5	
NUMBER OF PINS	DIM.A	DIM.B	DIM.C	



2PIN

耐 压: 1000V AC/minute

- 1) 材质:见附表;
- 2) 电镀:见附表;
- 3) 塑件表面平整、光洁、无毛刺、气泡、烧焦、变形、浇口无拉伤、多料或缺料等不良现象;
- 4) 端子表面无氧化、电镀不良等现象。

 韩下 HANXIA 深圳市韩下电子有限公司							
DRAW :	黄彬	2020-8-28	TITLE: HX-XH2.54-3PZZ-M SERIES: 1501 SERIES P/N:		DRAW NAME:		
DESIGN:		2020-8-28			插件针座		
CHECK:	张伟	2020-8-28					
APPROVED	罗小春	2020-8-28					
CUSTOMER DRAWING			REV. 1.00	SCALE N/A	UNIT: mm	SHEET: 1/1	

GENERAL TOLERANCES			
DIM	TOL	DIM	DEG
X.		X°	±3.00°
X.X	±0.35	X.X°	±2.00°
X.XX	±0.25	X.XX°	±1.00°
X.XXX	±0.15	X.XXX°	