







Circuit diagram



PCB Layout recommended

| NO.1    |        |
|---------|--------|
| PART NO | vigor  |
| 2       | 130±30 |
| 3       | 160±30 |
| 4       | 250±30 |

| NO.3-NO.4 |               |
|-----------|---------------|
| PART NO   | NOTE          |
| 01~99     | SERIAL NUMBER |

| NO.2    |               |
|---------|---------------|
| PART NO | MATERIAL/QTY. |
| S       | SUS/1PC       |
| D       | SUS/2PCS      |

|      |           |         |      |                 |           |        |
|------|-----------|---------|------|-----------------|-----------|--------|
| ⑤    | TERMINAL  | —       | 4    | Phosphor Bronze | Ag-PLATED | —      |
| ④    | Shell     | —       | 1    | SUS             | Natural   | —      |
| ③    | Contact   | —       | 1    | Stainless Steel | Ag-PLATED | —      |
| ②    | Base      | —       | 1    | LCP             | Black     | —      |
| ①    | Keystoke  | —       | 1    | LCP             | Black     | —      |
| ITEM | PART NAME | TER'NO. | QTY. | MATERIAL        | FINISHING | REMARK |

|                |       |        |           |             |                                                                                       |                                                                                             |  |
|----------------|-------|--------|-----------|-------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------|--|
| APPROVALS      |       |        | DATE      |             |  |                                                                                             |  |
| DRAWN          |       | LIUCAN | 2021.8.13 |             |                                                                                       |                                                                                             |  |
| CHECKED        |       |        |           | TITLE:      |                                                                                       | TACT SWITCHS                                                                                |  |
| APPROVALS      |       |        |           | PART NO.    |                                                                                       | K2-1114SN-A□□W-□□                                                                           |  |
| TOLERANCES ARE | 30~以上 | ±0.30  | ANGLE     | UNIT: mm    | SCALE: 1:1                                                                            | PROJ:  |  |
|                | 10~30 | ±0.20  |           |             |                                                                                       |                                                                                             |  |
|                | 5~10  | ±0.15  |           |             |                                                                                       |                                                                                             |  |
|                | ~ 5   | ±0.10  |           |             |                                                                                       |                                                                                             |  |
|                |       |        | ±2'       | DRAWING NO. | _____                                                                                 | SHEET 1 OF 1                                                                                |  |

|         |      |       |              |         |        |        |
|---------|------|-------|--------------|---------|--------|--------|
| —       | A    | —     | NEW          | —       | —      | —      |
| ECN NO. | REV. | DATE. | DESCRIPTION. | CHANGE. | CHECK. | APPRO. |