




材质及电镀

触点材料：磷青铜

螺丝：M2 钢 镀锌

塑件：PA66 UL94V-0

电气性能

额定电压：300V

额定电流：8A

接触电阻：20m

绝缘电阻：5000/1000V

耐电压：AC1500V/1min

机械性能

温度范围：-40 ° C~+105 ° C

瞬时温度：+250 ° C 5秒

剥线长度：5-6mm

		new		2015/5/3		A		瀚源	
ECN BO.		DESCRIPTION.		DATE.		REV.			
DESIGNED	CHECKED	APPROVAL	DRAWING NUMBER				SCALT: 1/2	SCALE: 3:1	
Mikey	Tom	Jerry	PART NAME	2EDGK-3.81-XXP	UNLESS OTHERWISE		X. ±0.25		
			MODEL NAME	2EDGK-3.81-XXP	SPECIFIED,TOLERANCE:	X.x ±0.20			
						X.xx ±0.15			
3RD ANGLE PROJ			HanElectricity Co.,LTD				FILE.NO.		