




P.C.B LAYOUT

技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: $-25^{\circ}\text{C} \sim 85^{\circ}\text{C}$ 。
3. 额定电压: 50V, AC, DC。
4. 接触电阻: $\leq 0.02\Omega$ 。
5. 绝缘电阻: $\geq 100\text{M}\Omega$ 。



Pin	A	B	C	D
2	1.25	4.40	3.20	/
3	2.50	5.65	4.45	
4	3.75	6.90	5.70	2.50
5	5.00	8.15	6.95	3.75
6	6.25	9.40	8.20	5.00
7	7.50	10.65	9.45	6.25
8	8.75	11.90	10.70	7.50
9	10.00	13.15	11.95	8.75
10	11.25	14.40	13.20	10.00
11	12.50	15.65	14.45	11.25
12	13.75	16.90	15.70	12.50
13	15.00	18.15	16.95	13.75
14	16.25	19.40	18.20	15.00
15	17.50	20.65	19.45	16.25
16	18.75	21.90	20.70	17.50

APPROVALS					DATE		DEALON 德隆® ELECTRONICS CO.,LTD			
DRAWN		G.M.Chen		2015/7/17		TITLE: 1.25mm Crimp Style Connectors				
CHECKED						PART NO. 1.25-XXA				
APPROVALS						UNIT: mm SCALE: 1:1 SHEET 1 OF 1				
TOLERANCES ARE		30 $\pm$ 0.15		$\pm$ 0.30		ANGLE		DRAWING NO.		
		10 $\pm$ 0.10		$\pm$ 0.20						
		5 $\pm$ 0.10		$\pm$ 0.15						
		~ 5		$\pm$ 0.10						
ECN NO.		REV.		DATE.		DESCRIPTION.		CHANGE. CHECK. APPRO.		
		A				NEW				