









P.C.B LAYOUT
TOP VIEW

Rating: 0.5A 30V DC
Contact Resistance:100 m Ω Max.
Operating temperature:-20 $^{\circ}$ C~70 $^{\circ}$ C
Operating force:3~20N
Operating Life:5,000cycles

SCHEMATIC



ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			

APPROVALS		DATE
DRAWN	G.M.Chen	2018/3/15
CHECKED		
APPROVALS		

DEALON
ELECTRONICS CO.,LTD

TOLERANCES ARE		30 $\pm$ 0.15 10 $\pm$ 0.20 9 $\pm$ 0.10 ~ 5 $\pm$ 0.10	$\pm$ 0.30 $\pm$ 0.20 $\pm$ 0.15	ANGLE	$\pm$ 2 $^{\circ}$	PART NO.	DC-002F-130	SCALE:	1:1	SHEET	1 OF 1
						UNIT: mm					
						DRAWING NO.					