



CUSTOMER(客户):			PAGE: 1 OF 2																																																														
ITEM: LCD75-6.8UH			Customer's ITEM:																																																														
Item 项目	Spec.(mm) 规格值	Typ. 实测值	1. MECHANICAL DIMENSIONS(外形尺寸): 																																																														
A	7.0± 0.3	7.0																																																															
B	7.8± 0.3	7.82																																																															
C	5.0± 0.3	5.02																																																															
D																																																																	
E																																																																	
F																																																																	
G																																																																	
H																																																																	
I	ref																																																																
J	ref																																																																
Marking(印字) 6R8																																																																	
2.ELECTRICAL CHARACTERISTICS(电特性要求): <table><tr><th>ITEM (项目)</th><th>Specifications(规格值)</th><th>Typ.(参考值)</th><th colspan="3">Test equipments(测试仪器)</th></tr><tr><td>L</td><td>6.8UH ± 20%</td><td></td><td colspan="3">TH2817B</td></tr><tr><td>Test Freq.</td><td>@100kHz 0.25V</td><td></td><td colspan="3">TH2817B</td></tr><tr><td>DCR</td><td>40mΩ MAX</td><td></td><td colspan="3">VR131</td></tr><tr><td>R.Current</td><td>3.5A</td><td></td><td colspan="3">VR126</td></tr><tr><td>Q.Min</td><td></td><td></td><td colspan="3"></td></tr><tr><td>Ope.Temp.</td><td>-20℃ TO 80℃</td><td></td><td colspan="3"></td></tr><tr><td>Others</td><td>10pcs</td><td></td><td colspan="3"></td></tr><tr><td></td><td></td><td></td><td colspan="3"></td></tr><tr><td></td><td></td><td></td><td colspan="3"></td></tr></table>						ITEM (项目)	Specifications(规格值)	Typ.(参考值)	Test equipments(测试仪器)			L	6.8UH ± 20%		TH2817B			Test Freq.	@100kHz 0.25V		TH2817B			DCR	40mΩ MAX		VR131			R.Current	3.5A		VR126			Q.Min						Ope.Temp.	-20℃ TO 80℃					Others	10pcs																
ITEM (项目)	Specifications(规格值)	Typ.(参考值)	Test equipments(测试仪器)																																																														
L	6.8UH ± 20%		TH2817B																																																														
Test Freq.	@100kHz 0.25V		TH2817B																																																														
DCR	40mΩ MAX		VR131																																																														
R.Current	3.5A		VR126																																																														
Q.Min																																																																	
Ope.Temp.	-20℃ TO 80℃																																																																
Others	10pcs																																																																


CUSTOMER(客户):	PAGE: 2 OF 2
ITEM: LCD75-6.8UH	Customer's ITEM:

◆、卷盘尺寸 (单位:mm)



A	2.3±0.2
B	10.75±0.2
C1	330±1
D	φ100±0.2
H	16.5±0.2
T	2.3±0.2
颜色	蓝色

◆、载带尺寸 (单位:mm)



项目	W	P	P0	T
规格	16.00	12.00	4.00	0.40
公差	±0.3	±0.1	±0.1	±0.05