



技术要求 Specification:

- 1、材质 Material: 磷铜 Phosphor copper, 厚度 Thickness: $0.6\pm0.03\text{mm}$;
- 2、表面处理 Surface treatment: 电镀锡 Electroplated tin;
- 3、未注公差 Undeclared tolerance: $\pm0.1\text{mm}$;
- 4、符合RoHS环保要求 Complies with RoHS environmental requirements, 盐雾时间48H , with a salt spray time of 48 hours;
- 5、包装方式 Packaging method: 载带包装 Carrier packaging.
- 6、焊锡要求 Solder requirements: $260^{\circ}\text{C}\pm10^{\circ}\text{C}$

未注尺寸公差 Unmarked dimensional tolerance standards:
线性 Linear:
0.5-3 ±0.1
>3-6 ±0.15
>6-30 ±0.2
>30-120 ±0.3
>120-400 ±0.5
>400-1000 ±0.8
角度 angle: $\pm5^{\circ}$

标记	更改前	更改后	日期			材 料		品 名		STEIPU 深圳市斯泰普科技有限公司 Shenzhen STEIPU S&T Co.Ltd.			
①						料 厚							
②						比 例	1:1						
③						单 位	mm	制 图	石玉林	2024-6-5	Part No. :STHW4-DU-PS18X80206		
④				视 角		校 对							
							审 核					图 幅	A4