

Notes:

1. Material:

1.1 Housing: thermoplastic high temp.
UL94V-0; Color: Natural.

1.2 Actuator: thermoplastic high temp.
UL94V-0; Color: black.

1.3 Terminal: copper alloy.

1.4 Fitting Nail : copper alloy.

2. Finish:

2.1 Terminal:

50u" Min. Nickel underplated overall.

1:1u"Gold on contact and solder area.

2.2 Fitting Nail:

50u" Min. Nickel underplated overall.

80~150u" Matte Tin plated.

3. Product must comply HF RoHS specification.

4. Product No:

5001-FPC 05 10 - ** R 1-00

ALTERNATE

PACKING R:卷;T:管

PIN








HIGH:1.0

PITCH:0.5

翻盖下接

JME CONNECTOR SERIES

CKT	DIM A	DIM B	DIM C	DIM D
4	3.77	1.50	2.60	3.27
5	4.27	2.00	3.10	3.77
6	4.77	2.50	3.60	4.27
7	5.27	3.00	4.10	4.77
8	5.77	3.50	4.60	5.27
9	6.27	4.00	5.10	5.77
10	6.77	4.50	5.60	6.27
11	7.27	5.00	6.10	6.77
12	7.77	5.50	6.60	7.27
13	8.27	6.00	7.10	7.77
14	8.77	6.50	7.60	8.27
15	9.27	7.00	8.10	8.77
16	9.77	7.50	8.60	9.27
17	10.27	8.00	9.10	9.77
18	10.77	8.50	9.60	10.27
19	11.27	9.00	10.10	10.77
20	11.77	9.50	10.60	11.27
21	12.27	10.00	11.10	11.77
22	12.77	10.50	11.60	12.27
23	13.27	11.00	12.10	12.77
24	13.77	11.50	12.60	13.27



RECOMMENDED FPC DIMENSION

RECOMMENDED P.C.B. PATTERN LAYOUT

CUSTOMER DRAWING

Tolerance Unspecified (未注公差)	Size(图幅): A4
0.0 ±0.35 0° ±5°	Unit(单位): MM
0.00 ±0.25 0°0 ±3°	Scale(比例): 1:1
0.000 ±0.15 0°00 ±1°	Project View (投影视角)
1 OF 1	Page(页数): A

深圳市文章济美科技有限公司

Shenzhen wenzhangjimei technology co., LTD

Product Name(产品名称):

0.5Pitch H=1.0 FPC Easy-on R/A TYPE 2 SMT CONN.

Product No(产品料号):

5001-FPC0510-**-R1-00

Designer(设计):

张孝雄





Checked(审核):

Approved(核准):

Rev	Date	Revisor
A	2020/10/26	张孝雄
版本	日期	制/修订人

NOTES:

1. 10 SPROCKET HOLE PITCH CUMULATIVE TOLERANCE.±0.20mm
2. CARRIER CAMBER NOT TO EXCEED 1mm IN 250mm.
3. ALL DIMENSIONS MEET EIA-481-C REQUIREMENTS.
4. MATERIAL: BLACK ANTI-STATIC POLYSTYRENE.
5. THICKNESS: 0.30 ± 0.05 mm.
6. PACKING LENGTH PER 13" REEL : 42.60METERS.
7. COMPONENT LOAD PER 13" REEL : 3500PCS.
8. PEELING OFF FORCE OF TOP TAPE 0.1N~0.7N(10.2gf~71.4gf).



6	4.97	16+0.3/-0	16.4	7.5±0.10	单边孔
8	5.97				
10	6.97				
12	7.97				
24	13.97	24+0.3/-0	24.4	11.5±0.10	

CLASSIFICATION DIMENSION(尺寸类别): FAI(首次检验): ② To ③ ■ "MARK IS MAJOR DIM(重点尺寸标示)" ⊗ "MARK IS CRITICAL DIM(Cpk&Cp标示)"		深圳市文章济美科技有限公司 Shenzhen wenzhangjimei technology co., LTD		
Tolerance Unspecified (未注公差): 0.0 ±0.10 0° ±3° 0.00 ±0.05 0° 0' ±2° 0.000 ±0.02 0° 00' ±1°		Size(图幅): A4 Unit(单位): MM Scale(比例): 1:1		Product Name(产品名称): 0.5Pitch H=1.0 FPC 掀盖卧式4代SMT型. 载带
Project View (投影视角): 1 OF 1 Rev(版本): 1.0		Page(页数): 1 OF 1 Rev(版本): 1.0		Product No(产品料号): EB-445XXX130-00
		Drawing No(图面编号): DNE00***.*		Date(日期): 2020/10/24
		Designer(设计): 吴小光		Checked(审核): Approved(核准):

1.0	初版发行	2020/10/24	吴小光
Rev	Change Description	Date	Revisor
版本	变更内容	日期	制/修订人