







REV.	MATTER	APP.	DATE
A			



NOTE:
 1.MATERIAL:
 a.HOUSING:THERMOPLASTIC GLASS FIBRE UL94V-0
 b.CONTACT:PHOSPHOR BRONZE
 (SURFACE PLATING: Ni 100u")
 SEE ORDERING INFORMATION
 2.ELECTRIC:
 a.CONTACT RESISTANCE: 30 MILLIOHMS MAX
 b.INSULATION RESISTANCE: 1000 MEGA OHMS MIN
 c.DIELECTRIC VOLTAGE: 750V AC ONE SEC LEVEL
 d.OPERATING TEMPERATURE: -55°C~ +85°C



PCB Holes Diagram
Top View



TOLERANCE		Tolerance: Unless otherwise specified			
LINEAR .x ±1 .x ±0.38 .xx ±0.25 .xxx ±0.10 ANGLE .x' ±5° .x' ±2° .xx' ±1°	3	TERMINAL-2	PHOSPHOR BRONZE	Ni-Plated	
	2	TERMINAL-1	PHOSPHOR BRONZE	Ni-Plated	
	1	HOUSING	PA66	BLACK	
	NO.	PART NAME	MATERIAL	COLOR/FINISHED	



深圳市连欣科技有限公司

Shenzhen City Lianxin Technology Co. LTD

日期DATE	单位UNITS	审核CHECK	PART NO: XDBS-CR2032-5
2019.8.28	mm		
比例SCALE	制图 DRAW	设计DESIGN	TITLE: BS-CR2032-5 立式直插3PIN电池座DIP
1/1			