





注: 未经允许禁止传播、复制、编辑该文档, 以及利用其内容进行交流

REV	E.C.N NO.	CONTENT	CHK	DATE



PCB Layout



NOTES1:

UL Standard

1.	Use group	B	C	D
	Rated Current	15A	/	10A
	Rated Voltage	300V	/	300V

2.withstanding voltage: AC1600V/1Min

IEC Standard

1.	Pollution Degree	3	2	2
	Overvoltage Category	III	III	II
	Rate Impulse Voltage(KV)	/	4.0KV	/
	Rate Voltage(V)	/	400V	/
	Rate Current(A)	/	15A	/

NOTES2:

1.Housing: PA66 (UL94V-0)

2.Solder Pin: Brass (Sn Plated)

NOTES3:

1.Pitch: 7.62mm Poles: 02-24P

2.Operating temperature: $-40^{\circ}\text{C} \sim +105^{\circ}\text{C}$

3.RoHS Compliance

How to order

MX2EDGV	-	7.62	-	XXP	-	XXXX	-	X	-	X	
产品型号		间距		极数		颜色:		01:常规颜色		A-Z其他定制	
						02-99:		定制颜色			
						灰色:GY		橙色:OE		Cu:铜	
						蓝色:BU		红色:RD		Fe:铁	
						黑色:BK		透明色:TT			
						绿色:GN		黄色:YW			
						白色:WE					

Pitch Range In mm			Nominal Dimension Range In mm					—	⌒	▤
TO 6	Over 6 TO 10	Over 10 TO 24	TO 30	Over 30 TO 60	Over 60 TO 100	Over 100 TO 150	Over 150	0.1/10		
±0.15	±0.20	±0.30	±0.30	±0.50	±0.70	±1.00	±1.30	±2°		

ITEM	NAME OF PART		NO. OF PART	Q"TY	MATERIAL		NOTE	
DWG.	CKK	DATE	23.06.20	UNITS	MM	SHEET/OF	1/1	
CHK.		DATE		SCALE	1:1	A4		
APP.		DATE			NAME MX2EDGV-7.62-XXP			
CIXI MAIXU ELECTRONICS CO.,LTD.					DWGNO.			
慈溪市迈旭电子有限公司								