








REV.	ECN NO.	REVISED	DATE



PCB Layout Diagram
Top View




技术要求:











- 1、截断面毛刺高度 $\leq 0.03\text{mm}$;
- 2、部件要求平整,无变形、裂纹、损伤等外观缺陷;

UNLESS OTHERWISE SPECIFIED TOLERANCES		MYOUNG 美阳 www.meiyoungdz.com			
DECIMALS:	ANGLES:	DSND	Huanglieqing	DATE	2021-11-25
X : ±0.30	X : ±1°	CHKD	ZhouRuicai	DATE	2021-11-25
X.X : ±0.25	X.X : ±0.5°	APVD	XueShun Yong	DATE	2021-11-25
X.XX : ±0.20		WEIGHT:	SCALE:	SIZE: A4	VIEW:
X.XXX : ±0.10		SHEET 1 OF 2	UNIT: mm	REV.: A/0	OBJECT: MY
				TITLE:	电池扣CR2032-P Ni DIP 卷装
				PART NO.:	MY-2032-18-R
				DRAW NO.:	MY-CP-0295

1	TERMINAL+	1	C5191 T=0.25mm	Ni-Plating
NO.	PART NAME	Q'TY	MATERIAL	PLATING & COLOR



产品



技术要求:

- 圆孔十个孔距离累计允许公差为 $\pm 0.2\text{mm}$
- 带长250mm内容许弯曲度1mm
- 材料厚度以在载带边缘测量为准
- 所有尺寸定义依循EIA-481-C系准则定义之
- 材料: 透明PS T=0.4mm
- 所有卷轮为灰蓝挖空旋转塑胶卷轮
- 整模成型长度: 9.4M,
- 非指明公差范围为: $\pm 0.1\text{mm}$; 超过250mm不计累计误差
- 型腔外形凡未标明处倒角R为0.2-0.3; 拔模斜度未标注的为 3° 以下

包装信息:

- 每卷盘装产品 450 只, 卷盘外侧贴相关标签;
- 每 6 卷盘放在一个塑料袋中;
- 每外箱装6盘, 产品总数: 2700 只;
- 外箱上下用胶纸封成"工"字;
- 电池扣包材CR2032-P DIP 卷装(MY-2032-P-DIP-R)。

工程部
2024-08-26
H. WANG

UNLESS OTHERWISE SPECIFIED TOLERANCES		MYOUNG 美阳 www.meiyangdz.com			
DECIMALS:	ANGLES:	DSND	WangHeng	DATE	2024-08-26
X : ±***	X : ±***	CHKD	ZhouRuicai	DATE	2024-08-26
X.X : ±***	X.X : ±***	APVD	XueShunYong	DATE	2024-08-26
X.XX : ±***	X.XX : ±***	WEIGHT:	SCALE:	VIEW:	VIEW: ① ②
X.XXX : ±***	X.XXX : ±***	SHEET 2 OF 2	UNIT: mm	REV.: A/0	OBJECT: MY
				TITLE:	
				电池扣CR2032-P Ni DIP 卷装	
				PART NO.:	
				MY-2032-18-R	
				DRAW NO.:MY-BD-0087	