



REV.	ECN NO.	REVISED	DATE

NOTE:

1.MATERIAL:

a.HOUSING:LCP UL94V-0

b.CONTACT:PHOSPHOR BRONZE

(SURFACE PLATING: Sn100u"-120u")

SEE ORDERING INFORMATION

2.ELECTRIC:

a.CONTACT RESISTANCE: 50 MILLIOHMS MAX

b.INSULATION RESISTANCE: 100 MEGA OHMS MIN

c.DIELECTRIC VOLTAGE: 500V AC ONE SEC LEVEL

d.OPERATING TEMPERATURE: -25°C~ +85°C

ORDERING INFORMATION

BS-24-B***014

电池座系列

BS-24系列

SMT 180° TYPE

PLATING:

A-Au1U"

J-Ni100U"~120U"

K-Sn100U"~120U"

MATERIAL:

1A-PBT BLACK

1B-PA66 BLACK

2A-PPA BROWN

2B-PPA BLACK

3A-PPS BROWN

3B-PPS BLACK


4A-LCP WHITE

4B-LCP BLACK

工程部

2022-03-26

LQ. HUANG



PCB Layout Diagram
Top View

③	TERMINAL(-)	1	PHOSPHOR BRONZE, T=0.20mm	Sn Plating and Ni Under-Plating
②	TERMINAL(+)	1	PHOSPHOR BRONZE, T=0.20mm	Sn Plating and Ni Under-Plating
①	HOUSING	1	LCP	BLACK
NO.	PART NAME	Q'TY	MATERIAL	PLATING & COLOR

UNLESS OTHERWISE SPECIFIED TOLERANCES		MYOUNG 美用 www.meiyangdz.com					
DECIMALS:	ANGLES:	DSND	YangFeng	DATE	2022-03-26	TITLE:	
X :±0.30	X :±1°	CHKD	ZhouRuicai	DATE	2022-03-26	BS-2450-4 Sn SMT LCP黑色	
X.X :±0.25	X.X :±0.5°	APVD	XueShunyong	DATE	2022-03-26	PART NO.:	
X.XX :±0.20		WEIGHT:	4.72g	SCALE:1.5:1	SIZE: A4	VIEW:	BS-24-B4BK014
X.XXX :±0.10		SHEET 1 OF 1		UNIT: mm	REV.: A/0	OBJECT: MY	DRAW NO.:MY-CP-0297