







注: 未经允许禁止传输、复制、编辑该文档, 以及利用其内容进行交流

REV	E.C.N NO.	CONTENT	CHK	DATE



Frist poles



NOTES1:

UL Standard

1.

Use group	B	C	D
Rated Current	8A	/	8A
Rated Voltage	300V	/	300V

IEC Standard

1.

Pollution Degree	3	2	2
Overvoltage Category	III	III	II
Rate Impulse Voltage(KV)	/	/	2.5KV
Rate Voltage(V)	/	/	250V
Rate Current(A)	/	/	7A

NOTES2:

- 1.Housing: PA66 (UL94V-0)
- 2.Nut: Brass
- 3.Pin Header: Copper alloy (Sn Plated)

NOTES3:

- 1.Pitch: 3.81mm Poles: 02-24P
- 2.Stripping length: /
- 3.Operating temperature: $-40^{\circ}\text{C} \sim +105^{\circ}\text{C}$
- 4.RoHS Compliance

How to order

MX15CDGV	- 3.81	- XXP	- XXXX	- X	- X
产品型号	间距	极数	颜色:	01:常规颜色	A-Z其他定制
			灰色:GY	橙色:OE	02-99:
			蓝色:BU	红色:RD	定制颜色
			黑色:BK	透明色:TT	
			绿色:GN	黄色:YW	
			白色:WE		
				Cu:铜	
				Fe:铁	

Pitch Range In mm			Nominal Dimension Range In mm					—	∩	□
TO	Over 6	Over 10	TO	Over 30	Over 60	Over 100	Over 150	0.1/10		
6	TO 10	TO 24	TO 30	TO 60	TO 100	TO 150		<		
±0.15	±0.20	±0.30	±0.30	±0.50	±0.70	±1.00	±1.30	±2°		

ITEM	NAME OF PART		NO. OF PART	Q"TY	MATERIAL		NOTE	
DWG.	CHK	DATE	23.07.20	UNITS	MM	SHEET/OF	1/1	A
CHK.		DATE		SCALE	1:1	A4		
APP.		DATE						
CIXI MAIXU ELECTRONICS CO.,LTD.				NAME	MX15CDGV-3.81-XXP			
慈溪市迈旭电子有限公司				DWGNO.				