







D		E		F		
版次	更新摘要	日期	序号	品名	材质	
0	新图制定	2022. 3. 25				
			①	0.5掀盖卧式带扣胶芯(H=2.55)	LCP UL94V-0 本色	
			②	0.5掀盖卧式后盖带扣(H=2.55)	LCP UL94V-0 黑色	
			③	0.5掀盖卧式端子带扣(H=2.55)	铜合金/表面镀金	
			④	0.5掀盖卧式焊片带扣(H=2.55)	铜合金/表面镀锡	




技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: -25° C~85° C.
3. 额定电流: 0.5A
4. 额定电压: 50V, AC.
5. 接触电阻: 50mΩ MAX.
6. 绝缘电阻: 500MΩ Min.
7. 耐电压: 150V AC/1Minute
8. 产品料号: 5001 -FPC 05 25 -** R 0 0

JM FPC CONNECTOR SERIES
PITCH: 0.5
HIGH: 2.55
ALTERNATE
PACKING: R: 卷
PIN



SECTION A-A
SCALE 1:1



一般公差 (TOLERANCE)
X ±0.50 .XX ±10
X ±0.20 .XXX ±05
ANGLES ±1°

深圳市文章济美科技有限公司				
品名 (TITLE)		制图 (DR)		
0.5 Pitch掀盖卧式下接带扣(H=2.55)业务图		校对 (CHKD)		
料号 (DWG.NO)		审核 (APPD)		
5001-FPC0525-**R1-00		张数 (SHEET)		
比例 (SCALE)		单位 (UNITS)		SIZE
1:1		mm		REV
		1 OF 2		A4 A

