


承 認 書
SPECIFICATION FOR APPROVAL

NO: YF90053A



尺寸數據(mm)	
A	3.5 ± 0.2
B	6.0 ± 0.2
C	0.55 ± 0.5
D	12.5
E	2.0 ± 0.2
F	5.0 ± 0.5
G	4.0 ± 0.5
H	18.5 ± 0.85
J	12.5 ± 0.3
W	18 ± 0.85
W1	10 ± 1.8

DIMENSION 尺寸			MATERIAL 材料			TESTING CONDITION 測試條件	CUSTOMER 客戶
Measuring unit: mm			R10			測試儀器: E4991A	
OD	3.50	±0.3	30mhz-35 Ω	初始磁導率	680	1-500MHZ	
ID	0.80	±0.3	100mhz-60 Ω	比損耗因子	≤17 (0.1mhz)	0.5x0.5TSx100L(mm)	
HT	6.00	± 0.8		飽和磁通密度	280(1600A/m)	DATE: 2025/4/1	