

2		1		
REV	E.C.N NO.	CONTENT	CHK	DATE



Use group	B	C	D
Rated Current	5A	/	/
Rated Voltage	150V	/	/

2.withstanding voltage: AC1300V/1Min

1. Pollution Degree	3	2	2
Overvoltage Category	III	III	II
Rate Impulse Voltage(KV)	1.5KV	2.5KV	2.5KV
Rate Voltage(V)	80V	160V	200V
Rate Current(A)	5A	5A	5A

1.Housing: PA66 (UL94V-0)
2.Solder Pin: Brass (Sn Plated)

1.Pitch: 2.5mm Poles: 02-24P
2.Operating temperature: -40℃~+105℃
3.RoHS Compliance

MX2EDGR - 2.5 - XXP - XXXX - XX - X

产品型号 间距 极数 01:常规颜色 02-99:定制颜色 A-Z其他定制

颜色: 灰色:GY 橙色:OE 定制颜色 Cu:铜
蓝色:BU 红色:RD Fe:铁
黑色:BK 透明色:TT
绿色:GN 黄色:YW
白色:WE

ITEM	NAME OF PART		NO. OF PART	Q"TY	MATERIAL		NOTE	
DWG.	CKK	DATE	24.01.07	UNITS	MM	SHEET/OF	1/1	
CHK.		DATE		SCALE	1 : 1	A4		
APP.		DATE		NAME	MX2EDGR-2.5-XXP			
 CIXI MAIXU ELECTRONICS CO., LTD. 慈溪市迈旭电子有限公司								
DWGNO.								