



Mounting Hole Layout









Terminal Arrangement (Bottom View)

TOP



SPDT/DPDT Contacts
(SPDT contacts on the right only)

PC Board Drilling Layout (Bottom View)



(Δ) Bezel Style: Round(1), Square(2), Rectangular(3),
Rectangular with 3-way barriers(4)




(◇) Operation Type: Momentary(M), Alternate(A)

(□) Contact arrangement: Gold contact 1C(1), Gold contact 2C(2),
Silver contact 1C(5), Silver contact 2C(6)

(◎) Terminal Style: Tab Terminal(Blank), PC Board Terminal(V)

(*) Button Color: Red(R), Green(G), Black(B), White(W),
Yellow(Y), Blue(S)

Lens Type: Red(LR), Green(LG), Black(LB), Amber(LA),
White(LW), Yellow(LY), Blue(LS)



Product Name: LB SERIES PUSHBUTTONS

Type Number: LB ΔB—◇1T□◎*

Approved by M.FUJIMOTO

Apr. 25, 2024

Checked by Y.HANAOKA

Apr. 25, 2024

Drawn by F.TAKAI

Apr. 25, 2024

Dim.: mm

Outside View

Drawing No. MA4-H02030C