







接触区域镀金

焊接区域及其他区域镀雾锡



P.C.B LAYOUT

#### Specifications:

规格:

Voltage rating:250V AC/DC

额定电压: 250V AC/DC

Current rating:2A AC/DC

额定电流: 2A AC/DC

Withstanding voltage:500V AC/minute

耐受电压: 500V AC/分钟

Temperature range:-40℃~+105℃

温度范围: -40℃~+105℃

Insulation resistance:≥1000MΩ

绝缘电阻: ≥1000MΩ

Contact resistance:≤20mΩ

接触电阻: ≤20mΩ

Material:PA6T UL94V-0

材质: PA6T UL94V-0

Plating Category:1U"Gold

镀层: 1U"Gold

Wave soldering temperature:255±5℃, 10S

波峰焊温度: 255±5℃, 10S

X4621 W R - 2xXX B - C40 D28

① ② ③ ④ ⑤ ⑥ ⑦

1.Series No.

2.Category:W-Water

3.Welding Board Angle:R-Stright 90°

4.Row No -Pin No:2xXX-2x02P-2x40P

5.B:B-Type B

6.Pin Length: C=4.0mm

7.Pin Length:D=2.8mm

|                      |                 |               |             |                         |
|----------------------|-----------------|---------------|-------------|-------------------------|
| X4621WR-2xXXB-C40D28 | PA6T<br>UL94V-0 | Brass         | 1U"Gold     | X4621H                  |
| PART NO              | Material        | Material(Pin) | Finish(Pin) | Suitable XKB<br>Housing |

|                                      |  |             |                                     |
|--------------------------------------|--|-------------|-------------------------------------|
| DSND                                 |  | SCALE: N/A  | MODEL TYPE:<br>2.00mm BTB Connector |
| DWN                                  |  | VIEW:       | PART NO.:<br>X4621WR-2xXXB-C40D28   |
| CHKD                                 |  | UNIT: mm/in | DWG NO.:<br>X-X4621WR-2xXXB-C40D28  |
| APPD                                 |  | SIZE: A4    |                                     |
| KXB INDUSTRIAL PRECISION CO.,LIMITED |  |             | WEIGHT                              |
|                                      |  |             | SHEET                               |
|                                      |  |             | REVISION                            |
|                                      |  |             | 1/1                                 |
|                                      |  |             | A0                                  |

XKLB

|                                               |                        |
|-----------------------------------------------|------------------------|
| 广东星坤科技股份有限公司                                  |                        |
| 建                                             | 日期                     |
| 效                                             |                        |
| 审                                             |                        |
| MARK                                          | 文件工程章                  |
| DESCRIPTION                                   | REVISIONS              |
| DATE                                          | REVISED                |
| APPROVED                                      | UNSPECIFIED TOLERANCES |
| www.helloxkb.com www.helloxkb.cn www.xk-dg.cn |                        |

|          |      |
|----------|------|
| ANGULAR  | ±5°  |
| L≤ 4     | ±0.2 |
| 4<L≤ 16  | ±0.3 |
| 16<L≤ 63 | ±0.4 |
| L> 63    | ±0.5 |