






RoHS
Compliant






Notes:

- 1.Current Rating: 12V&1A max.
- 2.Contact Resistance: 50mOhms Max.(initial)
- 3.Insulation Resistance: 100M Ohms Min./500V DC
- 4.Dielectric Withstanding Voltage: 500V AC/1Minute
- 5.Mating Force: 35N Max, Withdrawal Force: 3N Min.
- 6.Durability: 5,000 Cycles
- 7.Operating Temperature:-25°C to+85°C



RECOMMEND PCB LAYOUT
TOLERANCE:±0.05

Circuit Diagram



8	Cover
7	Housing
5	Spring Contact
4	Left Contact
3	Right Contact
2	Mic Contact
1	Ground Contact

Thermoplastics	Black
Copper Alloy	Sn On Solder&Contact Area;Ni Plated Overall. G/F On Contact Area Sn On Solder Tails Ni Plated Overall.

Item	Name	Material	Description
DRAWING:	林生财	DATE:	2025.02.15
CHECK:	李宏鑫	DATE:	2025.02.15
APPROVAL:	杨进宝	DATE:	2025.02.15
DRAWING NO.	ZB23040-05DBAP-C	SHEET	1/1



LZG INDUSTRIAL CO. LTD

PART NAME	Audio Jack 5Pin Sink Type W/ Switch (SMD)	TOLERANCE UNLESS	0.0±0.30	0.°±2°	UNIT:	mm
PART NO.	ZB23040-05DBAP-C	OTHERWISE SPECIFIED:	0.00±0.20 0.000±0.10	0.0°±1° 0.00°±0.5°		