







RoHS
Compliant

ZONE	EC N.O.	DESCRIPTION	DRAWING	DATE
A		INITIAL	林生财	2020.02.18





* MATERIAL

TERMINAL 1 : COPPER ALLOY
TERMINAL 2 : COPPER ALLOY
TERMINAL 3 : COPPER ALLOY
TERMINAL 4 : COPPER ALLOY
TERMINAL 5 : COPPER ALLOY
SHIELD : STAINLESS STEEL
SUPPORT : BRASS
HOUSING : HIGH TEMP. PLASTIC
COVER : HIGH TEMP. PLASTIC



RECOMMENDED PCB LAYOUT
TOLERANCE: ± 0.05
(TOP VIEW)

SCHEMATIC



Ø3.5 MATE PLUG

LZG

LZG INDUSTRIAL CO. LTD

DRAWING:	林生财	DATE:	2020.02.18	SCALE:	1:1
CHECK:	李宏鑫	DATE:	2020.02.18	MATERIAL:	*
APPROVAL:	杨进宝	DATE:	2020.02.18	DWG. NO.	
DRAWING NO.	ZB23038-07SBAP-A			SHEET	1/1

PART NAME	WATERPROOF Ø3.5 PHONE JACK	TOLERANCE UNLESS	0.0±0.3	0.°±2°	UNIT:
PART NO.	ZB23038-07SBAP-A	OTHERWISE SPECIFIED:	0.00±0.2	0.0°±1°	
			0.000±0.1	0.00°±0.5°	