




RoHS
Compliant






3D VIEW




ZONE	E C N . N O .	DESCRIPTION	DRAWING	DATE
A		INITIAL	林生财	2020.02.18

SPECIFICATIONS:


1. CURRENT RATING: 3.0A MAX
2. DIELECTRIC WITHSTAND VOLTAGE: 100VAC
3. TEMPERATURE RANGE: -30 °C ~ 85 °C
4. CONTACT RESISTANCE: 40 MILLIONHM MAX
5. INSULATION RESISTANCE: 100 MEGOHMS MIN.
6. INSERTION FORCE : 5N~20N
7. UNMATING FORCE: 8N~20N
8. DURABILITY:10,000 CYCLES



建议胶圈尺寸



RECOMMENDED PCB LAYOUT(TOP VIEW)
(GENERAL TOLERANCE±0.05)



结构设计注意:

成品使用时, 如有洗面奶泡沫、牙膏、洗手液、脏污液体, 请在TYPE-C口外面再设计一层外壳, 保护TYPE-C表面金手指不会被脏污覆盖。

A1	GND	B12	GND	6	WATERPROOF RING	SILICA GEL	COLOR BLACK	1
A4	VBUS	B9	VBUS	5	SHELL	STAINLESS STEEL	Ni PLATING	1
A5	CC1	B8	SBU2	4	SHIELDING PLATE	STAINLESS STEEL	Ni PLATING	1
A6	DP1	B7	DN2	3	CONTACT	COPPER ALLOY	Au/Ni PLATED	16
A7	DN1	B6	DP2	2	SHELL HOUSING	HIGH TEMPERATURE PLASTIC	COLOR BLACK	1
A8	SBU1	B5	CC2	1	HOUSING	HIGH TEMPERATURE PLASTIC	COLOR BLACK	1
A9	VBUS	B4	VBUS					
A12	GND	B1	GND					
PIN	SIGNAL NAME	PIN	SIGNAL NAME	NO.	DESCRIPTION	MATERIAL	REMARKS	QTY






LZG INDUSTRIAL CO. LTD

DRAWING:	林生财	DATE:	2020.02.18	SCALE	1:1
CHECK:	李宏鑫	DATE:	2020.02.18	MATERIAL	*
APPROVAL:	杨进宝	DATE:	2020.02.18	DWG. NO.	
DRAWING NO.	ZB48024-16DBAP-A			SHEET	1/1

PART NAME	WATERPROFF TYPE C 16PIN	TOLERANCE UNLESS	0.0±0.3	0.1'±2'	UNIT:	mm
PART NO.	ZB48024-16DBAP-A	OTHERWISE SPECIFIED:	0.00±0.1	0.0'±1'		
			0.000±0.05	0.00'±0.5'		

RoHS
Compliant

ZONE	ECN.N.O.	DESCRIPTION	DRAWING	DATE
A		INITIAL	林生财	2020.02.18



1. 包装方式



- 1-1: 使用半自动包装机, 先将 CARRY TAPE 送入导轨中, 并与 COVER TAPE 贴合在上面, 其中前端大于10空槽不要放产品, 尾端大于10空槽不要放产品, 然后将产品如图示方向依次放入 CARRY TAPE 每个槽放1PCS;
- 1.2. 用胶带将 CARRY TAPE 愈合在一起, 包装后在图示指定位置贴上 LABEL;
- 1-3: 按图示要求将10盘包装好的 REEL 装入纸箱, 纸箱上下按图示要求加垫海绵垫, 四角折三角垫固定;
- 1-4: 将装好产品的纸箱按图示要求封箱, 在指定区域贴好 LABEL;

2. 包装数量:

550PCS/REEL;
10REEL (5500PCS)/CARTON.

3. 耐剥离性:

上带引拔力测试规格: 20-150gf
测试条件: 以每分钟300mm速度引拔测试



8	气泡垫	L=345,W=345,T=10	2PCS
7	纸板(折三角垫)	L=430,W=330,T=6	4PCS
6	硬纸板	L=330,W=330,T=6	2PCS
5	外箱	L=350,W=350,H=330	1PCS
4	卷盘	PS,BLUE,A=330,B=100,W=32.4	10PCS
3	上带	PET,CLEAR,W=21.3	6.5m
2	载带	PS,BLACK,W=24,T=0.4,P=16	6.5m
1	CONN	CONN	5500PCS
NO.	NAME	SPEC	Q'TY

LZG

LZG INDUSTRIAL CO. LTD

DRAWING:	林生财	DATE:	2020.02.18	SCALE	1:1
CHECK:	李宏鑫	DATE:	2020.02.18	MATERIAL	*
APPROVAL:	杨进宝	DATE:	2020.02.18	DWG. NO.	
DRAWING NO.	ZB48024	PACKING DRAWING	SHEET	1/1	

PART NAME	WATERPROFF TYPE C 16PIN	TOLERANCE UNLESS	0.0±0.3	Q:±2°	UNIT:	
PART NO.	ZB48024-16DBAP-A	OTHERWISE SPECIFIED:	0.00±0.1	0.0°±1°	mm	
			0.000±0.05	0.00°±0.5°		