






Specifications:

Electrical:

- 1.Current Rating
1.5A/contact terminal
- 2.Voltage Rating
30V DC
- 3.Contact Resistance
30 milliohms MAX
- 4.Dielectric Withstanding Voltage:
500 V AC AT Sea Level
- 5.Insulation Resistance:
1000MEGA ohms MIN

Mechanical:



- 1.Connector Mate and Unmate Force
Mate force:3.75kgf(MAX)
Unmate force:1.02kgf(MIN)
- 2.Terminal Retention
1.2kgf(MIN)

Material:

- 1.Housing:
Hing Temperature Ternmaplastics,
UI 94V-0 PBT White
- 2.Contact:Copper Alloy C2680
- 3.Shell: Copper Alloy C2680/SPCC

Finish:

- 1.Contact: Plated Gold in Mating Area;
Tin On Solder Talls.
- 2.Shell:
Nickel Plating



RECOMMENDED PCB LAYOUT

GENERAL TOLERANCE ±0.05

MANUFACTURE DWG		 东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd	
UNLESS OTHERWISE SPECIFIED TOLERANCES			TITLE: USB B/F 90°DIP(弯脚)
			PAR USB-B10-BRW
DECIMALS:	ANGLES:		DWN Lucas
X.:±0.30	X.':±3°		CHKD Ethan
X.X:±0.20	X.X':±2°		APVD Jacob
X.XX:±0.10		CUSTOMER COPY	SCALE1:1 UNIT:MM
			SIZE:A4 SHEET:1F1
			REV:A