



RoHS  
Compliant

| ZONE | EC N.O. | DESCRIPTION | DRAWING | DATE       |
|------|---------|-------------|---------|------------|
| A    |         | INITIAL     | 林生财     | 2020.02.18 |

Notes:

- 1.Current Rating: 20V&15A max.
- 2.Contact Resistance: 50mOhms Max.(initial)
- 3.Insulation Resistance: 100M Ohms Min./500V DC
- 4.Dielectric Withstanding Voltage: 500V AC/1Minute
- 5.Mating Force: 35N Max, Withdrawal Force: 3N Min.
- 6.Durability: 3,000 Cycles
- 7.Operating Temperature: -25°C to +85°C



LZG®

LZG INDUSTRIAL CO. LTD

|             |                  |       |            |          |     |
|-------------|------------------|-------|------------|----------|-----|
| DRAWING:    | 林生财              | DATE: | 2020.02.18 | SCALE    | 1:1 |
| CHECK:      | 李宏鑫              | DATE: | 2020.02.18 | MATERIAL | *   |
| APPROVAL:   | 杨进宝              | DATE: | 2020.02.18 | DWG. NO. |     |
| DRAWING NO. | ZB30017-02DBAP-A |       |            | SHEET    | 1/1 |

|           |                  |                      |           |            |          |  |
|-----------|------------------|----------------------|-----------|------------|----------|--|
| PART NAME | 5525 大电流DC公头     | TOLERANCE UNLESS     | 0.0±0.3   | 0.°±2°     | UNIT: mm |  |
| PART NO.  | ZB30017-02DBAP-A | OTHERWISE SPECIFIED: | 0.00±0.2  | 0.0°±1°    |          |  |
|           |                  |                      | 0.000±0.1 | 0.00°±0.5° |          |  |