





RoHS
Compliant

ZONE	EC N. NO.	DESCRIPTION	DRAWING	DATE
A		INITIAL	林生财	2025.02.15



Notes:

- 1.Current Rating: 12V&1A max.
- 2.Contact Resistance: 30mOhms Max.(initial)
- 3.Insulation Resistance: 100M Ohms Min./500V DC
- 4.Dielectric Withstanding Voltage: 500V AC/1Minute
- 5.Mating Force: 35N Max, Withdrawal Force: 3N Min.
- 6.Durability: 10,000 Cycles
- 7.Operating Temperature:-25°C to+85°C



7	Housing	Thermoplastics	Black
6	6#Pin Contact	Copper Alloy	Sn On Solder&Contact Area;Ni Plated Overall.
5	5#Pin Contact		
4	4#Pin Contact		G/F On Contact Area Sn On Solder Tails Ni Plated Overall.
3	3#Pin Contact		
2	2#Pin Contact		
1	1#Pin Contact		
Item	Name	Material	Description

LZG

LZG INDUSTRIAL CO. LTD

DRAWING:	林生财	DATE:	2025.02.15	SCALE	1:1
CHECK:	李宏鑫	DATE:	2025.02.15	MATERIAL	*
APPROVAL:	杨进宝	DATE:	2025.02.15	DWG. NO.	
DRAWING NO.	ZB23039-06DBAP-B			SHEET	1/1

PART NAME	Hifi 3.5mm Audio Jack 6Pin W/ Switch(CH=3.25mm)	TOLERANCE UNLESS	0.0±0.30	0.°±2°	UNIT: mm	
PART NO.	ZB23039-06DBAP-B	OTHERWISE SPECIFIED:	0.00±0.20	0.0°±1°		
			0.000±0.10	0.00°±0.5°		