






RoHS
Compliant

Pb
Lead free

ZONE	E C N . N O .	DESCRIPTION	DRAWING	DATE
A		INITIAL	林生财	2025.01.14



RECOMMEND PCB LAYOUT
TOLERANCE:±0.05

Notes:

- 1.Current Rating: 24V&3A max.
- 2.Contact Resistance: 30mOhms Max.(intial)
- 3.Insulation Resistance: 100M Ohms Min./500V DC
- 4.Dielectric Withstanding Voltage: 500V AC/1Minute
- 5.Mating Force: 35N Max, Withdrawal Force: 3N Min.
- 6.Durability: 5,000 Cycles
- 7.Operating Temperature:-25°C to+85°C

3	Shell(-)	Copper Alloy	Ni On Contact
2	Center Pin(+)	Thermoplastics	&Solder Area(See P/N)
1	Housing	Black	
Item	Name	Material	Description

LZG

LZG INDUSTRIAL CO. LTD

DRAWING:	林生财	DATE:	2025.01.14	SCALE	1:1
CHECK:	李宏鑫	DATE:	2025.01.14	MATERIAL	*
APPROVAL:	杨进宝	DATE:	2025.01.14	DWG. NO.	
DRAWING NO.	ZB30019-04DBAP-B			SHEET	1/1

PART NAME	DC POWER JACK	TOLERANCE UNLESS	0.0±0.30	0.°±2°	UNIT:	mm
PART NO.	ZB30019-04DBAP-B	OTHERWISE SPECIFIED:	0.00±0.20	0.0°±1°		
			0.000±0.10	0.00°±0.5°		