






RoHS
Compliant


Notes:

- 1.Current Rating: 12V&1A max.
- 2.Contact Resistance: 30mOhms Max.(initial)
- 3.Insulation Resistance: 100M Ohms Min./500V DC
- 4.Dielectric Withstanding Voltage: 500V AC/1Minute
- 5.Mating Force: 35N Max, Withdrawal Force: 3N Min.
- 6.Durability: 5,000 Cycles
- 7.Operating Temperature:-25°C to+85°C


ZONE	EC N.O.	DESCRIPTION	DRAWING	DATE
A		INITIAL	林生财	2025.02.15



RECOMMEND PCB LAYOUT
TOLERANCE:±0.05



Circuit Diagram((For 4Pole Plug))



10	Cover	Thermoplastics	Black
9	Housing		
8	Separator		
7	Spring	stainless steel	
6	Switch B Contact	Copper Alloy	Sn On Contact Area &Solder Tails
5	Switch A Contact		
4	Left Contact		G/F On Contact Area Sn On Solder Tails Ni Plated Overall.
3	Right Contact		
2	Mic Contact		
1	Ground Contact		

LZG

LZG INDUSTRIAL CO. LTD

DRAWING:	林生财	DATE:	2025.02.15	SCALE	1:1
CHECK:	李宏鑫	DATE:	2025.02.15	MATERIAL	*
APPROVAL:	杨进宝	DATE:	2025.02.15	DWG. NO.	
DRAWING NO.	ZB23041-06FBAP-E			SHEET	1/1

PART NAME	Audio Jack 6Pin W/ Switch(SMD Type)	TOLERANCE UNLESS	0.0±0.30	0.°±2°	UNIT: mm
PART NO.	ZB23041-06FBAP-E	OTHERWISE SPECIFIED:	0.00±0.20	0.0°±1°	

0.000±0.10 0.00°±0.5°