







标 记 MARK	ECN编号/变更内容 ECN NO/DEFINITION	修 改 REVISE	日 期 DATE	核 准 APPROVE

A1	GND	B12	GND
A4	VBUS	B9	VBUS
A5	CC1	B7	DN2
A6	DP1	B6	DP2
A7	DN1	B5	CC2
A9	VBUS	B4	VBUS
A12	GND	B1	GND
PIN	SIGNAL NAME	PIN	SIGNAL NAME



A1	A4	A5	A6	A7	A9	A12
B12	B9	B7	B6	B5	B4	B1



RECOMMENDED P.C.B. LAYOUT
TOLERANCE UNSPECIFIED ±0.05mm

- 备注:
1. 电气性能:
- 1.1 接触电阻: 30mΩ Max FOR INITIAL.
40mΩ Max AFTER TEST.
- 1.2 耐电压:100V AC
- 1.3 绝缘:100MΩ Min
- 1.4 额定电流:
- COLLECTIVELY VBUS PIN (A4, A9, B4, B9),
TOTAL 5A
- VCCON PIN (B5) THROUGH GND
PIN(A1, A12, B1, B12), 1.25A
- OTHERS PIN, 0.25A
- 1.5 工作温度: -40° C ~ 80° C.
2. 机械性能:
- 2.1 插入力: 5~20N.
- 2.2 拔出力: 初始值8~20N测试后6~20N
- 2.3 寿命: 10,000 CYCLES

3	外壳	不锈钢	镀镍	
2	接触	铜	镀金	
1	基座	LCP	黑色	
序 号	品 名	材 质	电镀/颜色	备 注



深圳市虹成电子有限公司

品 名 TITLE	TYPE-C母座
料 号 PART NO	HC-TYPE-C-14P-LC01E

GENERAL TOLERANCES (UNLESS SPECIFIED)	比 列 SCALE	1:1	制 图 DRAW		
X. ±0.30 X.* ±2*	单 位 UNIT	MM	审 核 CHECKED	夏操云	
.X ±0.20 .X.* ±1*	张 数 PART NO	1 OF 1	批 准 APPROVE	赵亮亮	
.XX ±0.15 .XX.*	版 本 REV	A			
.XXX ±0.05 .XXX.*					