





规格说明:Specifications:
电气特性:Electrical:
1. 额定电流: Current Rating
5A/contact terminal
2. 额定电压: Voltage Rating
30V DC
3. 接触阻抗:Contact Resistance
30 milliohms MAX
4. 耐电压:Dielectnic Withstanding Voitage:
500 V AC AT Sea Levol
5. 绝缘阻抗:Lnsulation Resistance:
1000MEGA ohms MIN
物理性能:Mechanical:
1. 插拔力: Cnnector Mate and Unmate Force
Mate force:3.57kgf (MAX)
Unmate force:1.02kgf (MIN)
2. 端子保持力: Terminal Retenion
1.2kgf (MIN)
原材料:Matorial:
1. 塑胶:Housing:
Hing Temperature Tnermaplastics,
9T Orange
2. 端子:Contact:Copper Alloy C7025
3. 外壳:Shell: Copper Alloy C2680
电镀:Finish:
1. 端子:Contact: Piated Gold in Mating Area;
Tin On Solder Talls
2. 外壳:Shell:
Nickel Plating

3	外壳	铜	镀镍	
2	接触	铜	镀金	
1	基座	PA9T	橙色	
序 号	品 名	材 质	电镀/颜色	备 注

		深圳市虹成电子有限公司		品 名		USB座		
				TITLE				
				料 号		HC-USB2. 0-L100-093P		
				PART NO				
GENERAL TOLERANCES (UNLESS SPECIFIED)		比 列 SCALE	1 : 1					
X. X ±0.30 X. XX ±0.20 X. XXX ±0.10 X° ±5° X. X° ±2°		单 位 UNIT	MM	制 图 DRAW	AhYe			
		张 数 PART NO	1 OF 1	审 核 CHECKED	夏操云			
		版 本 REV	A	批 准 APPROVE	赵亮亮			

