





SECTION A-A



SECTION B-B

SPECIFICATIONS

- 1、Current Rating: 60A AC, DC
- 2、Voltage Rating: 630V AC, DC
- 3、Temperatuer Range: -40℃~ +105℃
- 4、Contact Resistance: 10mΩ Max
- 5、Insulation Resistance: 1000mΩ Min
- 6、Withstanding Voltang: 3000V AC/minute
- 7、Material: Phosphoric bronze Tin-plated
- 8、Applicable Wire Sizes:AWG#8-20#

Part NO.	Dimensions mm					适配线规
	A1	B1	A2	B2	C	AWG
HC-10.16-T-A-05(低脚)	4.75	5.10	3.50	3.00	3.00	#16-20
HC-10.16-T-05	5.50	6.00	3.50	3.70	3.50	#16-14
HC-10.16-T-B-05(高脚)	6.80	7.70	4.80	4.80	5.00	#12-10
HC-10.16-T-C-05(高脚)	11.10	9.60	6.20	6.20	5.00	#8

			GENEERL TOLERANCE	制 图 DRAWING	 深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO.,LTD			
			DIM TOL	审 核 CHECK				
			X.X ±0.30	批 准 APPROVAL	产品名称 TITLE	10.16 母端子	版 本 REV.	A
1	初版发行		X.XX ±0.20	比 例 SCALE	产品料号 PART NO.	HC-10.16-T-05	单 位 UNITS	mm
序号 No.	变更内容 MODIFY CONTENT	日 期 MODIFY DATE	X.XXX ±0.10	投 影 Projection	材 料 MATERIAL		页 次 SHEET	1/1
			Angle ±3.0°					