

客户名称: CUSTOMER							
我司料号: OUR PART NO.							
我司品名: OUR PART NAME							
送样日期: DATE SAMPLES	数 量: QUANTITY						
	制造确认	. MANUFACT	URER APPRO	OVE			
拟制 DRA	WN	审核 CHEC	KED	确认 APPROVED			
HuFangti	ing	RaoPin		Zhongcuilan			
	—————————————————————————————————————	的 CUSTOMI	ER APPROVI	E			
客户名称 CUSTO	OMER NAME:						
客户料号 CUSTO	OMER P/N:						
规格型号 DESCF	RIPTION:	XRAL0512	47uH ±10% 5	00mA			
检查結果: □	盖章:						
INSPECT RESU 说明 REMARK:	LT ACCEPT	REJECT	SIGNAT	TURE AND STAMP			

如对本承认书内容有异议请提出或标记发送至我司,本承认书在未收到异议回复时于本承认书提供一周后生效。

If you have any objection to the contents of this acknowledgement, please put forward or mark it and send it to our company. This acknowledgement will take effect one week after it is provided if you do not receive an objection reply.

东莞市祥如电子有限公司

Dongguan xiangru electronics co., ltd

Tel: 0769-86346548 Fax: 0769-86346358

Email: dgxiangru@126.com



客户名称 CUSTOMER		日期 DATE	2025-05-06
客户物料编号 CUSTOMER P/N		客户规格型号 DESCRIPTION	XRAL0512 47uH ±10% 500mA
我司物料编号 OUR PART NO	XRAL0512-470K	我司品名 OUR PART NAME	Color ring inductance

修订记录 Revision record


日期 Date	修改内容 Modify the content	审核 Checked	确认 Approved
2023/10/27	首次发行First issue	Zhongcuilan	Huangchuan gen



客户名称 CUSTOMER		日期 DATE	2025-05-06
客户物料编号 CUSTOMER P/N		客户规格型号 DESCRIPTION	XRAL0512 47uH ±10% 500mA
我司物料编号 OUR PART NO	XRAL0512-470K	我司品名 OUR PART NAME	Color ring inductance

外观尺寸 Appearance of size

单位 Unit: mm



ФА	5.0 MAX	В	12.0 MAX	C	0.6 ±0.1	
标识	Identification	依据	具体规格 号Acc	cording to	the specific	specification number

原理图Schematic Diagram:



注意事项 Matters needing attention:

- 1、由于油漆调配比例略有差异,烘烤时间及烘烤温度存有差异,不同批次或同一批次存有色差属正常现象: Due to the slight difference in paint blending ratio, there are differences in baking time and baking temperature, and it is normal for different batches or the same batch to have color difference:
- 2、不要使产品遭受温度和湿度的快速变化, 易造成电感涂层开裂, 建议使用温度范: -20~+125℃; Don't subject the product to rapid changes in temperature and humidity, which may easily lead to cracking of the inductor coating. It is recommended to use the temperature norm of-20 ~+125℃;
- 3、色环电感成品外观检查事项及标准详见以下附件: See the following attachments for the appearance inspection items and standards of finished products of color ring inductors:



					1				
客户名 CUSTOM						日期 DATE		2	025-05-06
客户物料 CUSTOME					客户规格型号 DESCRIPTION		XRAL0512 47uH ±10 500mA		
	我司物料编号 OUR PART NO XRAL0512-470F		K	我司品名 OUR PART NAME		Сс	Color ring inductance		
				电性	参数				
	Electrical parameters								
品名规格Com specifica	-	XRAL05			磁芯规格Magnetic core specification			Γ	DRWW4*8
漆包线enamel]	led wire	2UEW-0. 23mm		mposite mber	52.5T S	色环标识Color ring	1. `	-	貴 2.紫3.黑4.银 .Purple 3.Black4.Silver
测试项 TEST PRO		电性范 SP	EC	测量	试条件	TEST FREQ		测试仪器 TEST STRUMENTS	
电感量	ţL	47uH ± 10 9	%		at 25℃	1KHz/0.25V		TH2829A	
直流电阻	LDCR	0.4Ω ΜΑΣ	X		at 25℃	1KHz/0.25V		TH2829A	
饱和电流	[sat	L≥L0 909	%	at 25°CDC 556mA 1KHz/0.25V			TH2829A		
额定电i rated cur		500mA (±5%	(±5%)		at 25℃ 1KHz/0.25V			TH2829A	
			!	物料清	单 BO	M			
物料 MATERIA L	SP	规格型号 ECIFICATION	IS	制造厂商					UL证书号 UL FILE NO
CORE	Ferrite core 4*8			JIACHENG					
CORE	I	reffile core 4 ° 8		OR Equivalent supplier					
WIRE		2UEW-F(QA)		CHENGWE				E227475	
,,, IKE		202 ((1 (Q/1)		OR Equivalent supplier					
PIN	Tinned	Finned copper clad steel wire (CP)		BAICHUAN					
				OR Equivalent supplier					
EPOXY		DOT 1		QIFU					
PAINT	DGT-1(green)		OR Equivalent supplier						
EPOXY		D.Z. (JINGDINGSHENG					
RESIN		DZ-6			OR Equivalent supplier				
SOLDER	Sn	Sn:99.3%/Cu:0.7%		SONGBEN					
	2217710 TO WOOT 70		OR Equivalent supplier						



注意事项 Matters needing attention

1、本承认书保证我司产品作为一个单体时的质量情况,当我司产品被安装到贵司产品上时,请保证我司的产品已根据贵司的规范进行了有效评价和确认。

Specification for approval that guarantee the quality of our products as a monomer, when our products were installed on your products, please make sure that our products are according to your specification for the effective evaluation and confirmation.

2、 本承认书的更改需经双方确认,任何一方单独修改无效。

The recognition of the need to change the book recognized by both parties, either party to amend a separate as null and void.

3、本承认书在客户收到的七个工作日内,必须签章返回,逾期视为默认。

Admit in the book the customer received within seven working days, must return signature, late regarded as the default.

4、 该电感器磁芯的中部缠绕有漆包线并连接于两端引脚, 引脚成型过程中可能造成开路或损伤本体。当您执行引脚成型过程时,请遵守以下指示:

The middle part of the core of the inductor is wound with enameled wires and is connected with the pins at both ends. Pin forming process may cause open circuit or damage the body. When you perform the pin forming process, Please comply with the following instruction: Please apply supporting jigs as below

