



安装视图



TEL:0769-82310511-867

- Rating : DC36V 3A.
- Contact resistance: $\leq 50\text{m}\Omega$.
- Insulation resistance: $\geq 1000\text{M}\Omega$ (DC500V).
- Withstanding voltage: 2000VAC.
- Operating Force: $\leq 4\text{N}$
- life test: 50000 cycles.
- Operation temperature range: $-25^{\circ}\text{C} \sim 85^{\circ}\text{C}$.
- Sign"* "is importance dimension.

发光类型:E环形/DY电源符号/D单点/E+DY环形+电源符号/E+D环形+单点

发光颜色: R红/G绿/L蓝/Y黄/W白/O橙/P紫

额定电压: AC/DC:3V/6V/12V/24V/36V/48V/AC:60V/110V/220V

10	C/NO/NC TERMINAL	BRASS	3	Ag-PLATED
9	LED TERMINAL	BRASS	2	Ag-PLATED
8	CONTACT	SILVER ALLOY	2	
7	C/NO/NC HOUSING	PA46	1	
6	LED HOUSING	PC	1	
5	NUT	BRASS	1	Ni-PLATED
4	O-RING	SILICA GEL	1	BLACK
3	SHELL	SUS/BRASS	1	Ni-PLATED
2	BUTTON	SUS	1	
1	LUMINOUS REGION	PC	1	
NO.	PART NAME	MATERIAL	QTY	FINISHING

TOLERANCE UNLESS SPECIFIED								
<1.5: ±0.1mm	ANGULAR ±1°							
>1.5~5.0:±0.25mm								
>5.0:±0.3mm		NO	DATE	REVISIONS			BY	APPD
TITLE: PUSH SWITCH				UNIT : MM	ROHS	DWN		
MODEL: HY-22A-P11-N-E+DY-L12V-SU-008				SCALE: 1:1	COMPLIANT	CHK'D		
东莞市六钧电子五金有限公司						APPD		
						PRO.AGL:		