




轴视图



TEL: 0769-82310511-867



安装视图



- 1.Rating : DC36V 3A.
- 2.Contact resistance : $\leq 50\text{m}\Omega$.
- 3.Insulation resistance : $\geq 1000\text{M}\Omega$ (DC500V).
- 4.Withstanding voltage : 1500VAC .
- 5.Operating Force : $\leq 6\text{N}$
- 6.life test : 100000 cycles.
- 7.operation temperature range: $-25^{\circ}\text{C} \sim 85^{\circ}\text{C}$.
- 8.Sign "*" is importance dimension.

发光类型:E环形/DY电源符号/D单点状/E+DY环形+电源符号/E+D环形+单点状

发光颜色:R红/G绿/L蓝/Y黄/W白/O橙/P紫

灯电压:AC/DC:3V/6V/12V/24V/36V/48V/AC:60V/110V/220V

| | | | | |
|-----|-----------------------|--------------|-----|-----------|
| 9 | NO TERMINAL | BRASS | 2 | Ag-PLATED |
| 8 | LED TERMINAL | BRASS | 2 | Ag-PLATED |
| 7 | CONTACT | SILVER ALLOY | 2 | |
| 6 | HOUSING | PA66 | 1 | BLUE |
| 5 | NUT | BRASS | 1 | Ni-PLATED |
| 4 | O-RING | SILICA GEL | 1 | WHITE |
| 3 | SHELL | SUS/BRASS | 1 | Ni-PLATED |
| 2 | BUTTON | SUS | 1 | |
| 1 | LIGHT-EMITTING REGION | PC | 1 | |
| NO. | PART NAME | MATERIAL | QTY | FINISHING |

| TOLERANCE UNLESS SPECIFIED | | | REVISIONS | | | BY APPD |
|----------------------------------|--------------------------|-------------------------------|----------------------------|------------|-------|---------|
| | <1.5: $\pm 0.1\text{mm}$ | >1.5~5.0: $\pm 0.25\text{mm}$ | ANGULAR $\pm 1^{\circ}$ | NO | DATE | |
| TITLE: PUSH SWITCH | | | | ROHS | DWN | |
| MODEL:HY-19E-G10-N-E-G24V-SU-008 | | | | COMPLIANT | CHK'D | |
| | | | | SCALE: 1:1 | APPD | |

东莞市六钧电子五金有限公司

PRO.AGL: REV :A0