




NUT




SCHEMATIC



安装视图



轴视图



SPECIFICATION

- 1.Rating : DC36V 3A.
 - 2.Contact resistance: $\leq 50\text{m}\Omega$.
 - 3.Insulation resistance: $\geq 1000\text{M}\Omega$ (DC500V).
 - 4.Withstanding voltage: 2000VAC .
 - 5.Operating Force: $\geq 5\text{N}$
 - 6.Travel:自锁 $3.0\pm 0.1\text{mm}$ /复位 $2.5\pm 0.1\text{mm}$
 - 7.life test: 50000 cycles.
 - 8.Operation temperature range: $-25^{\circ}\text{C}\sim 85^{\circ}\text{C}$.
 - 9.Sign"* "is importance dimension.
- TEL:0769-82310511-867

8	C/NO/NC TERMINAL	BRASS	3	Ag-PLATED	TOLERANCE UNLESS SPECIFIED										
7	TERMINAL	SILVER ALLOY	2	Ag-PLATED											
6	C/NO/NC BASE	PA46	1		< 1.5: ±0.1mm > 1.5~5.0: ±0.25mm > 5.0: ±0.3mm	ANGULAR ±1°	A0	2024.5.31	首次发行			ZLK			
5	LED BASE	PC	1				NO	DATE	REVISIONS			BY	APPD		
4	NUT	BRASS	1	Ni-PLATED	TITLE: PUSH SWITCH			UNIT : MM		ROHS	DWN				
3	WASHER	RUBBER	1	WHITE	MODEL:HY-19A-P11-N-CU-008			SCALE: 1:1		COMPLIANT	CHK'D				
2	COVER	SUS/BRASS	1	BRASS:Ni-PLATED	东莞市六钧电子五金有限公司						APPD				
1	BUTTON	SUS	1												
NO.	PART	NAME	MATERIAL	QTY	FINISHING							PRO.AGL:			REV :A0