







无灯电气原理图



安装视图



- Rating : DC36V 3A.
 - Contact resistance: $\leq 50\text{m}\Omega$.
 - Insulation resistance: $\geq 1000\text{M}\Omega$ (DC500V).
 - Withstanding voltage: 1500VAC .
 - Operating Force: $\leq 3\text{N}$
 - life test: 50000 cycles.
 - Operation temperature range: $-25^\circ\text{C} \sim 85^\circ\text{C}$.
 - Sign "*" is importance dimension.
- TEL: 0769-82310511-867

8	C/NO/NC TERMINAL	BRASS	3	Au-PLATED	TOLERANCE UNLESS SPECIFIED						
7	CONTACT	SILVER ALLOY	2								
6	C/NO/NC HOUSING	PA46	1								
5	LED HOUSING	PC	1								
4	NUT	BRASS	1	Ni-PLATED							
3	O-RING	RUBBER	1	WHTIE							
2	SHELL	铝合金氧化黑	1								
1	BUTTON	铝合金氧化黑	1								
NO.	PART	NAME	MATERIAL	QTY	FINISHING						

TITLE: PUSH SWITCH
 UNIT : MM
 ROHS
 DWN
 MODEL: HY-25A-P11-S-CU-008
 SCALE: 1:1
 COMPLIANT
 CHK'D
 APPD
 APPD
 PRO.AGL: REV :A0

东莞市六钧电子五金有限公司