





1. Rating : DC36V 3A.
  2. Contact resistance:  $\leq 50\text{m}\Omega$ .
  3. Insulation resistance:  $\geq 1000\text{M}\Omega$  (DC500V).
  4. Withstanding voltage:  $2000\text{VAC}$  .
  5. Operating Force:  $\leq 3.5\text{N}$
  6. Travel: 按压到底行程:  $2.8 \pm 0.2\text{mm}$ /接触行程:  $1.5 \pm 0.1\text{mm}$ /  
NO脚反推力:  $\leq 30\text{N}$ /螺母力矩:  $5\text{--}14\text{N.m}$
  7. life test: 50000 cycles.
  8. Operation temperature range:  $-25^{\circ}\text{C} \sim 85^{\circ}\text{C}$ .
- TEL:0769-82310511-867



|     |                       |              |     |           |                                    |                |    |      |            |           |       |    |                                                                                                                                                                                              |  |  |
|-----|-----------------------|--------------|-----|-----------|------------------------------------|----------------|----|------|------------|-----------|-------|----|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--|--|
| 10  | C/NO/NC CONTACT FOOT  | BRASS        | 3   | Ag-PLATED | LED脚 公共脚 常开脚 常闭脚 LED脚A             |                |    |      |            |           |       |    |                                                                                                                                                                                              |  |  |
| 9   | LED CONTACT FOOT      | BRASS        | 2   | Ag-PLATED |                                    |                |    |      |            |           |       |    |                                                                                                                                                                                              |  |  |
| 8   | CONTACT               | SILVER ALLOY | 2   |           | TOLERANCE                          |                |    |      |            |           |       |    |                                                                                                                                                                                              |  |  |
| 7   | C/NO/NC HOUSING       | PA46         | 1   |           | UNLESS SPECIFIED                   |                |    |      |            |           |       |    |                                                                                                                                                                                              |  |  |
| 6   | LED HOUSING           | PBT          | 1   |           | <1.5: ±0.1mm                       | ANGULAR<br>±1° |    |      |            |           |       |    |                                                                                                                                                                                              |  |  |
| 5   | NUT                   | BRASS        | 1   | Ni-PLATED | >1.5~5.0: ±0.25mm                  |                |    |      |            |           |       |    |                                                                                                                                                                                              |  |  |
| 4   | O-RING                | RUBBER       | 1   | BLACK     | >5.0: ±0.3mm                       |                | NO | DATE | REVISIONS  |           |       | BY | APPD                                                                                                                                                                                         |  |  |
| 3   | SHELL                 | SUS/BRASS    | 1   | Ni-PLATED | TITLE: PUSH SWITCH                 |                |    |      | UNIT : MM  | ROHS      | DWN   |    |                                                                                                                                                                                              |  |  |
| 2   | BUTTON                | SUS          | 1   |           | MODEL: HY-16A-G11-S-DY-R12V-CU-008 |                |    |      | SCALE: 1:1 | COMPLIANT | CHK'D |    |                                                                                                                                                                                              |  |  |
| 1   | LIGHT-EMITTING REGION | PC           | 1   |           | 东莞市六钧电子五金有限公司                      |                |    |      |            |           |       |    | APPD                                                                                                                                                                                         |  |  |
| NO. | PART NAME             | MATERIAL     | QTY | FINISHING |                                    |                |    |      |            |           |       |    | PRO.AGL:   REV :A0 |  |  |