








CAD FILE:



SCHEMATIC (NON-SHORTING)

P.C.B. LAYOUT  
BOTTOM VIEW

8	STEEL BALL	STEEL	1	NATURAL	TOLERANCE UNLESS SPECIFIED WITHIN 1.5mm : ±0.1mm OVER 1.5mm : ±0.2mm	A	13-Jun-2015	初版		APPD.
7	SPRING	STEEL WIRE	1	NATURAL				DESCRIPTIONS OF REVISION		
6	CONTACT CLIP	PBS STRIP	2	Ag PLATED						
5	POSITION PLATE	STEEL STRIP	1	Ni PLATED						
4	TERMINAL	BRASS STRIP	6	Ag PLATED	TITLE : VERTICAL SLIDE SWITCH		UNIT : mm	DRWG NO.: XZ-DR-SS23F19-00		
3	BASE	PHENOLIC RESIN	1	NATURAL	MODEL: VS14-10122ZBZ-4		SCALE: 2:1	DWN.		
2	FRAME	STEEL STRIP	1	Ni PLATED				CHK'D		
1	KNOB	POM	1	BLACK				APPD.		
NO.	PARTS	MATERIALS	Q'TY	FINISH	东莞市六钧电子五金有限公司					