







SPECIFICATIONS

- 1、Current Rating: 7A AC, DC
- 2、Voltage Rating: 600V AC, DC
- 3、Temperatuer Range: -25℃~+85℃
- 4、Contact Resistance: 20mΩ Max
- 5、Insulation Resistance: 1000MΩ Min
- 6、Withstanding Voltang: 1500V AC/minute
- 7、Material: Wafer PA66, UL94V-2
PIN Brass Tin-plated



PIN	尺寸 (mm)	
	A	B
-02P	4.20	9.60
-03P	8.40	13.80
-04P	12.6	18.00
-05P	16.80	22.20
-06P	21.00	26.40

GENERAL TOLERANCE		制 图 Mapping	张迎春 2022、12、08		料 号 PART NO.	A42002-nP		版 本 REV.	A
X.±0.25	X.°±2°		审 核 Audit	钱岳生 2022、12、08		品 名 TITLE	5557 (5569) 单排公壳		页 次 SHEET
.X±0.25	.X°±1°	核 准 Approved		张 名 2022、12、09		客户料号 CUTM. NO.			
.XX±0.15	.XX°±0.5°		深 圳 市 金 航 标 电 子 有 限 公 司						
.XXX±0.10	.XXX°±0.5°	单 位 Units			mm	比 例 SCALE			