


Qty	Dept
1	DC
1	ED
1	IE
1	ISO
1	PD
1	R&D
1	SD
1	QA
1	QC
1	QE

REV.	DESCRIPTION	DRAWN	CHECKED	APPROVED
A	NEW RELEASE	WPY 12/12/24'		



GENERAL TOLERANCE		ANGLE TOLERANCE		PROJECTION		TITLE	2.54mm Female Header V/T Type	
X. ±0.60		X. ±5°		UNITS	mm			
.X ±0.38		.X ±3°		SHEET SIZE	A4	SERIES	DS1023 SERIES	
.XX ±0.25		.XX ±2°		 晨翔电子有限公司 CONNFLY CONNFLY ELECTRONIC CO. LTD				
DRAWING TYPE	CUSTOMER							
SCALE	1:1	SHEET	1 OF 1					
DRAWING NO.	C-DS1023-XXXX-A							

备注:

1. 电性说明:
 - 1.1 耐压: 600伏交流电一分钟
 - 1.2 绝缘阻抗: 1000兆欧最小
 - 1.3 接触电阻: 最大20毫欧
 - 1.4 额定电流: 3安
 - 1.5 额定电压: 250V交流电
2. 环境特性:
 - 2.1 工作温度: $-40^{\circ}\sim+105^{\circ}\text{C}$
3. 材料:
 - 3.1 胶芯: PBT或PA-9T, 黑色, 阻燃
 - 3.2 端子: 铜合金, 镀金
4. 产品符合欧盟RoHS环保要求