


25.60 [1.008]

19.40 [0.764]



37


A diagram of a 16-pin D-sub connector. The pins are arranged in two rows of eight. The top row is labeled with the number '8' at the left end and '1' at the right end. The bottom row is labeled with the number '1' at the left end and '8' at the right end. A rectangular component is shown connected to the top row of pins.

8

—

19.40 [0.764]

Ø20.8 [0.819]





MAX 2mm

Δx		
Δx		
Δx		

MARK	DESCRIPTION
	文件工程章


广东星坤科技股份有限公司										DSND		DATE		SCALE: N/A	MODEL TYPE: RJ JACK		
Δ		日期					ANGLAR	±5°	DWN		DATE		VIEW: 	PART NO.: RJ45S-XKB08S			
Δ							4<L≤16	±0.3	CHKD		DATE		UNIT: mm/in	DWG NO.: RJ45S-XKB08S			
Δ							16<L≤63	±0.4	APPD		DATE		SIZE: A4				
MARK		DESCRIPTION	DATE	REVISED	APPROVED		L > 63	±0.5									
文件工程章							UNSPECIFIED TOLERANCES			XKB INDUSTRIAL PRECISION CO.,LIMITED				WEIGHT 1.0g	SHEET 1/1	REVISION A0	
www.xk-dg.cn www.helloxkb.com www.helloxkb.cn																	




Wierlist

P1	wire
1	orange/white
2	orange
3	green/white
6	blue
4	blue/white
5	green
7	brown/white
8	brown

广东星坤科技股份有限公司										DSND		SCALE: N/A	MODEL TYPE: RJ JACK					
生效日期	Δ		日期				ANGLAR	±5°	XKLB	DWN		VIEW: 	PART NO.: RJ45S-WM08SC					
	Δ						L ≤ 4	±0.2		CHKD		UNIT: mm/in	DWG NO.:					
	Δ						4<L≤ 16	±0.3		APPD		SIZE: A4						
							16<L≤ 63	±0.4										
MARK		DESCRIPTION				DATE	REVISED	APPROVED	L> 63	±0.5	XKB INDUSTRIAL PRECISION CO.,LIMITED			WEIGHT	SHEET	REVISION		
文件工程章		REVISIONS						UNSPECIFIED TOLERANCES							1/1	A0		
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn																		



Wierlist



广东星坤科技股份有限公司

Δ*

Δ*

Δ*


MARK

日期

文件工程章

REVISIONS	UNSPECIFIED TOLERANCES
ANGLAR	±5°
L≤ 4	±0.2
4<L≤ 16	±0.3
16<L≤ 63	±0.4
L> 63	±0.5

	DSND		SCALE: N/A	MODEL TYPE: RJ JACK		
	DWN		VIEW: 	PART NO.: RJ45S-WM08S		
	CHKD		UNIT: mm/in	DWG NO.:		
	APPD		SIZE: A4			
XKB INDUSTRIAL PRECISION CO.,LIMITED				WEIGHT	SHEET	REVISION
					1/1	A0



Note:
1.RoHS/REACH compliant
2.IP67

广东星坤科技股份有限公司	
Δ*	日期
Δ*	日期
Δ*	日期
MARK	文件工程章

				ANGLAR	±5°
				L≤ 4	±0.2
				4<L≤ 16	±0.3
				16<L≤ 63	±0.4
ON	DATE	REVISED	APPROVED	L> 63	±0.5
REVISIONS				UNSPECIFIED TOLERANCES	
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn					

XKB

XKB INDUSTRIAL PRECISION CO.,LIMITED

DSND	SCALE: N/A	MODEL TYPE:
DWN	VIEW:	PART NO.: PCN1316-28UN-1
CHKD	UNIT: mm/in	DWG NO.:
APPD	SIZE: A4	
WEIGHT	SHEET 1/1	REVISION A0