


REV	DESCRIPTION OF CHANGE	REVIEWED BY	ISSUE DATE
A	FIRST ISSUE	X.YAN	2023-03-28



NOTES:



1.MATERIAL: COPPER ALLOY, NICKEL PLATED,THICKNESS 0.25mm

2.PACKAGING: TRAY PACKAGING



3.TEMPERATURE RANGE:

OPERATING : -40°C TO +85°C

NON OPERATING : -55°C TO +105°C





TITLE SFP28 1X2 CAGE			CND-tek 深圳磁联达电子有限公司 Shen zhen cnd-tek Electronics Co., Ltd			
PART NO. SFP28 21434511 1X2Y			GENERAL TOLERANCE		UNIT:MM	SIZE: A4
APPROVE	CHECK	DRAW	.X±0.20	.X±1°	SCALE: 1:1	SHEET:1/4
QG.CHEN.	SL.WANG	X.YAN	.XX±0.15	.XX±5°		
			.XXX±0.10			





PCB LAYOUT
FOR SINGLE SIDE MOUNTING

TITLE SFP28 1X2 CAGE			CND-tek 深圳磁联达电子有限公司 Shen zhen cnd-tek Electronics Co., Ltd			
PART NO. SFP28 21434511 1X2Y			GENERAL TOLERANCE		UNIT:MM	SIZE: A4
APPROVE	CHECK	DRAW	.X±0.20	.X±1°	SCALE: 1:1	SHEET:2/4
QG.CHEN.	SL.WANG	X.YAN	.XX±0.15	.XX±5°		
			.XXX±0.10			





PCB LAYOUT
FOR BELLY TO BELLY SIDE MOUNTING

TITLE SFP28 1X2 CAGE			CND-tek 深圳磁联达电子有限公司 Shen zhen cnd-tek Electronics Co., Ltd		
PART NO. SFP28 21434511 1X2Y			GENERAL TOLERANCE		UNIT:MM
APPROVE	CHECK	DRAW	.X±0.20	.X±1°	SCALE: 1:1
QG.CHEN.	SL.WANG	X.YAN	.XX±0.15	.XX±5°	
			.XXX±0.10		
					SHEET:3/4
					REV:A



SECTION A-A

RECOMMENDED BEZEL DESIGN
SINGLE SIDED APPLICATIONS



SECTION A-A

RECOMMENDED BEZEL DESIGN
BELLY TO BELLY APPLICATIONS

TITLE SFP28 1X2 CAGE			CND-tek 深圳磁联达电子有限公司 Shen zhen cnd-tek Electronics Co., Ltd		
PART NO. SFP28 21434511 1X2Y			GENERAL TOLERANCE		UNIT:MM
APPROVE	CHECK	DRAW	.X±0.20	.X±1°	SCALE: 1:1
QG.CHEN.	SL.WANG	X.YAN	.XX±0.15	.XX±5°	SHEET:4/4
			.XXX±0.10		REV:A