






NOTES:


MATERIAL:
CAGE: COPPER ALLOY NI-PLATED, THICKNESS 0.25 MM
CONNECTOR:
PLASTIC HOUSING: HIGH TEMPERATURE LCP, UL94 V-0.
SPRING: STAINLESS STEEL, THICKNESS 0.20mm
LIGHT PIPE: POLYCARBONATE; COLOR: CLEAR
CONTACTS: PHOSPHOR BRONZE, THICKNESS 0.20mm
PLATING: 15 μ " MIN. GOLD ON MATING AREA,
150 μ " MIN. MATE TIN ON SOLDER TAILS.
PACKAGING: TRAY PACKAGING.
TEMPERATURE RANGE: -40°C TO +85°C



TITLE SFP28 2X4 CAGE+CONNECTOR			CND-tek 深圳磁联达电子有限公司 Shen zhen cnd-tek Electronics Co., Ltd		
PART NO. SFP28 2339978 2X4Y			GENERAL TOLERANCE		UNIT:MM
APPROVE	CHECK	DRAW	.X±0.20	.X±1°	SCALE: 1:1
QG.CHEN.	SL.WANG	X.YAN	.XX±0.15	.XX±5°	SHEET:1/3
			.XXX±0.10		REV:A



TITLE SFP28 2X4 CAGE+CONNECTOR			CND-tek 深圳磁联达电子有限公司 Shen zhen cnd-tek Electronics Co., Ltd		
PART NO. SFP28 2339978 2X4Y			GENERAL TOLERANCE		UNIT:MM
APPROVE	CHECK	DRAW	.X±0.20	.X±1°	SCALE: 1:1
QG.CHEN.	SL.WANG	X.YAN	.XX±0.15	.XX±5°	SHEET:2/3
			.XXX±0.10		REV:A



TITLE SFP28 2X4 CAGE+CONNECTOR			CND-tek 深圳磁联达电子有限公司 Shen zhen cnd-tek Electronics Co., Ltd		
PART NO. SFP28 2339978 2X4Y			GENERAL TOLERANCE	UNIT:MM	SIZE: A4
APPROVE	CHECK	DRAW	.X±0.20	SCALE: 1:1	SHEET:3/3
QG.CHEN.	SL.WANG	X.YAN	.XX±0.15		
			.XXX±0.10		
					REV:A