

P/N CODE:C86572

REV.	DESCRIPTION	DRAWN	CHECKED	APPROVED
A	NEW RELEASE	JLZ 06/12/16'	~	

NOTES:

1. ELECTRICAL CHARACTERISTICS:

1.1 CONTACT RESISTANCE: 20mΩ Max. INITIAL.

1.2 DIELECTRIC WITHSTANDING VOLTAGE: 500V AC(rms)
FOR 1 MINUTE.

1.3 INSULATION RESISTANCE: 1000MΩ Min.

2. ENVIRONMENT CHARACTERISTICS:

2.1 TEMPERATURE: -40°C~+105°C.

3. RESISTANCE TO SOLDERING HEAT: 260±5°C 5±0.5s.

4. PRODUCT NUMBER CODE:

DS1034-01- X X X X X X - JC

SCREW DIM. A
4: 4.80

SCREW TYPE
4: BRJ TYPE (W/O washer)


CONTACT PLATING
0: SELECTIVE GOLD FLASH

SHELL PLATING
N: FORNT SHELL NICKEL, BACK SHELL TIN

HOUSING COLOR
B: BLACK

CONNECTOR TYPE
F: FEMALE

No.OF CONTACTS
09: 9pos.



GENERAL TOLERANCE		ANGLE TOLERANCE		PROJECTION	UNIT	TITLE	
X.	±0.60	X.	±5°		mm	D-SUB DIP STRAIGHT WITH FORK TYPE	
.X	±0.38	.X	±3°				
.XX	±0.25	.XX	±2°				
DRAWING TYPE		CUSTOMER		SHEET SIZE		SERIES	DS1034-01 SERIES
SCALE		1:1	SHEET	1 OF 1			
DRAWING NO.		C-DS1034-01-XXXXXX-JC-A					