

REV.	ECN NO.	DESCRIPTION	DATE	DESIGN

备注:

1. 材质:

1.1 胶芯: LCP+30%G, F UL94V-0

1.2 端子: C7025 : 镍底50U" MIN

接触区域镀金 (AU 1u") 焊接区域镀金G/F

1.3 外壳: SUS304, T=0.30mm; 表面镀镍30U" MIN

1.4 芯片: SUS301;

2. 主要特性:

2.1 额定电流: 5A

2.2 接触阻抗: 40mΩ MAX (初始值)

50mΩ MAX (测试后)

2.3 绝缘阻抗: 100MΩ MIN

2.4 耐压测试: 100V AC R M S

2.5 整体插入力: 5-20N 整体插入力: 5-20N (耐久后)

整体拔出力: 8-20N 整体拔出力: 6-20N (耐久后)









2.6 耐久: 10000次

2.7 耐高温: SMT回流焊 (峰值260° ±5°), 熔胶不能有泡, 融胶等不良, 变色, 翘曲变形在公差范围内。

2.8 电镀品须做焊锡测试, 粘锡面积达到95%以上:

2.9 盐雾测试: 24H MIN

3.0 工作温度: -25°C ~ +80°C



TOLERANCE	NAME(INTENDED USE) CUSTOMER DRAWING	DRAWING NO. Guangdong FYOU Precision Electronic Technology Co.,LTD.	
X.X ±0.30 X.° ±10°	PART NO. FY23-6TC162F410-A	TITLE: TYPE-C16P 立贴母座A款	A
.XX ±0.20 X.° ±8°			
.XXX ±0.10 X.X° ±5°	DESIGN: ZXW	DRAWG NO. FY23-6TC162F410-A	
UNITS mm			
MATERIAL	CHED:	SCALE 1:1	SHEET 1/2
FINISH	APPD:	REV. A	