



3x2 Pin




3x3 Pin




SPECIFICATIONS


- 1、Current Rating: 13A AC, DC
- 2、Voltage Rating: 300V AC, DC
- 3、Temperatuer Range: -40℃~ +105℃
- 4、Contact Resistance: 20mΩ Max
- 5、Insulation Resistance: 1000mΩ Min
- 6、Withstanding Voltang: 1500V AC/minute
- 7、Material: Housing Nylon66 UL94-V0(850℃)



3x4 Pin



3x5 Pin



Circuit	Part NO.	Dimensions mm				
		A	B	C	D	E
2	HC-63001-3x2EY-PF1-05	14.35	12.90	6.99	26.13	6.35
3	HC-63001-3x3EY-PF1-05	20.70				
4	HC-63001-3x4EY-PF1-05	27.05				
5	HC-63001-3x5EY-PF1-05	33.40				

Ordering Information

HC-63001 - N*** - * - ** - 05

Pin

Type

Colour

高阻燃

灼热丝

PF1=750℃不燃，

850℃滴落物不燃

PF2=850℃不燃

默认-透明

V-孔座

EY-母孔座

N-蓝色

P-紫色

Y-黄色

G-绿色

B-棕色

深圳市华灿天禄电子有限公司
ShenzhenhuacantianluELECTRONICS CO.,LTD

			GENEERL TOLERANCE	制 图 DRAWING				
			DIM TOL	审 核 CHECK				
			X.X ±0.30	批 准 APPROVAL	产品名称 TITLE	63001 (6.30)三排 母孔座 高阻燃 灼热丝	版 本 REV.	A
			X.XX ±0.20	比 例 SCALE	产品料号 PART NO.	HC-63001-3xNEY-PF1-05	单 位 UNITS	mm
			X.XXX ±0.10	投 影 Projection	材 料 MATERIAL		页 次 SHEET	1/1
1	初版发行		Angle ±3.0°					
序号 No.	变更内容 MODIFY CONTENT	日 期 MODIFY DATE						