










HC-63001-3x2Y-05






HC-63001-3x3Y-05



HC-63001-3x4Y-05



HC-63001-3x5Y-05



SPECIFICATIONS

- 1、Current Rating: 13A AC, DC
- 2、Voltage Rating: 300V AC, DC
- 3、Temperatuer Range: -40℃~ +105℃
- 4、Contact Resistance: 20mΩ Max
- 5、Insulation Resistance: 1000mΩ Min
- 6、Withstanding Voltang: 1500V AC/minute
- 7、Material: Housing Nylon66 UL94-V0(850℃)

Ordering Information

HC-63001 - N*** - * - ** - 05

Pin

Type

Colour

高阻燃

灼热丝

PF1-750℃ 不燃，

850℃ 滴落物不燃

PF2-850℃ 不燃

BR-棕色

深圳市华灿天禄电子有限公司
ShenzhenhuacantianluELECTRONICS CO., LTD

			GENEERL TOLERANCE	制 图 DRAWING	 深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO.,LTD					
			DIM TOL	审 核 CHECK						
			X. X ± 0.30	批 准 APPROVAL						
			X. XX ± 0.20	比 例 SCALE		产品名称 TITLE	63001 (6.30) 三排 孔座 高阻燃 灼热丝	版 本 REV.	A	
1	初版发行		X. XXX ± 0.10			产品料号 PART NO.	HC-63001-3xNY-PF1-05	单 位 UNITS	mm	
序号 No.	变更内容 MODIFY CONTENT	日 期 MODIFY DATE	Angle ± 3.0°	投 影 Projection		材 料 MATERIAL		页 次 SHEET	1/1	