




④	胶壳	A3002-2*XP
③	端子	X3001-T-PN
②	线材	UL1007-22#AWG 黑
①	线材	UL1007-22#AWG 红
物料明细表 Material list		

24P	2*12
22P	2*11
20P	2*10
18P	2*9
16P	2*8
14P	2*7
12P	2*6
10P	2X5
08P	2*4
06P	2*3
04P	2*2
PIN	PX

- 技术要求:
1. 所有材料需符合RoHS
 2. 端子头剥头2.5±0.2mm， 两端打X3001-T-PN端子， 按图示要求穿壳
 3. 线材与端子铆合拉力≥3.6KG
 4. 成品短路测试必须100%通过
 5. 绝缘阻抗30M ohm MIN
 6. 导通阻抗0.8 ohm MAX
 7. 测试电压DC300V 0.01s

										U41F		Z4Z	
										PIN		PX	
										APPROVALS		DATE	
										DRAWN		G.M.Chen	
										CHECKED		2015/5/29	
										APPROVALS			
										TOLERANCES ARE		ANGLE	
										30~0.15		±0.30	
										10~0.30		±0.20	
										5~10		±0.15	
										~ 5		±0.10	
										±Z			
										DRAWING NO.			
										UNIT: mm		SCALE: 1:1	
										SHEET 1 OF 1			
										PROJ.			
										ECN NO.			
										REV.			
										DATE.			
										NEW			
										DESCRIPTION.			
										CHANGE.		CHECK.	
										APPRO.			

3.0mm端子线 2*20" 双排公壳 红/黑双头同向/线长150mm	
-------------------------------------	--